



GE
Lighting



PAR 64

SUPER CP62 EXE MF 240V 1/6 BX

88536

Product information

PAR lamps provide a robust and flexible design solution for a wide range of applications. Choice of PAR36, PAR46, PAR56 or PAR64

- 3000 K or 4200 K colour temperature
 - Choice of beam widths
 - Excellent colour rendering
 - High efficiency combined with low operating costs
 - Robust and reliable
 - UV control
 - Easy retrofit
 - Colour consistent throughout life
 - Colour blends with halogen and fluorescent
-



Product data

Cap/Base	GX16d
Bulb Shape	PAR
Bulb Diameter [mm]	203.2
Maximum Overall Length [mm]	152.4
Net weight per piece [g]	965
Gross weight per piece [g]	1072
Brand	General Electric (GE)

Performance data

Colour Rendering Index (CRI) [Ra]	100
Nominal correlated colour temperature (CCT) [K]	3200
Nominal beam angle [°]	25
Nominal center beam candlepower (CBCP) [cd]	138000
Energy efficiency class (EEC)	C
Rated Life [h]	300
Nominal power [W]	1000
Nominal lamp voltage [V]	240

Electrical data

Weighted energy consumption [kWh/1000h]	1037.14
Coil type	C-13D
Dimming Capability	Yes
Ballast Required	No

Logistic data

DUN Code	10043168885369
EAN Code	0043168885362
Pack Quantity	6
Layer quantity	24 EUR, 30 UK
Layer quantity EUR	24
Layer quantity UK	30
Pallet quantity EUR (PC)	120
Pallet quantity UK (PC)	150
Outer case size	536 x 391 x 196 (mm)
Product status	Available

Application areas



Club and Disco

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

Disclaimer

Special purpose lamp – Stage Studio. Not suitable for household illumination.