

## Low profile transformer FLN 6/21



### Advantages

Minimum size at high output
Low height
Double input voltage for series or parallel connection
Double output voltage for series or parallel connection
Designed for high ambient temperatures
Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDensiFill resin encapsulation
Coil shell in 2-chamber technology
Self-extinguishing potting material


### Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As an isolating transformer for the safe electrical isolation of the input and output sides. The transformer may be used to set up protective separation as a protective measure.

As a safety isolating transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

### Circuit Diagram



### Standards



Mains transformer  
to: VDE 0570 Teil 2-1, DIN EN 61558-2-1, EN 61558-2-1, IEC 61558-2-1, UL 5085-1/-2, CSA 22.2 No.66

### Approvals



ENEC 10 (VDE), UL 5085-1/-2, CSA 22.2 No.66



## Low profile transformer FLN 6/21

Electrical data	
Type	FLN 6/21
Input	
Rated input Voltage	2 x 115 Vac
Rated frequency	50 - 60 Hz
Output	
Rated output voltage	2 x 21 Vac
Rated Power	6.0 VA
No-load voltage (app. x factor)	1.49
No-load loss (typ.)	0.75 W
Efficiency	62 %
Standards	
Classification	Mains transformer
Approvals	
Approvals	cURus, ENEC 10 (VDE)
Environment	
Ambient temperature max.	70 °C
Safety and protection	
Type	encapsulated
Class of Insulation System	B
Protection index	IP 00
Safety class (prepared)	II
Short circuit strength	non-short-circuit proof
Order numbers	
<b>Order Number</b>	<b>FLN 6/21</b>

Mechanical data	
Type	FLN 6/21
Terminal and mounting	
Terminals	Pins for printed circuit boards
Measures and weights	
Core type	UI 30/10,5
Weight	0.19 kg

