



Low profile transformer FLN 6/9

Electrical data		Type	FLN 6/9
Input			
Rated input Voltage			2 x 115 Vac
Rated frequency			50 - 60 Hz
Output			
Rated output voltage			2 x 9 Vac
Rated Power			6.0 VA
No-load voltage (app. x factor)			1.49
No-load loss (typ.)			0.75 W
Efficiency			62 %
Standards			
Classification			Safety isolating transformer
Approvals			
Approvals			cURus, ENEC 10 (VDE)
Environment			
Ambient temperature max.			70 °C
Safety and protection			
Type			encapsulated
Class of Insulation System			B
Protection index			IP 00
Safety class (prepared)			II
Short circuit strength			non-short-circuit proof
Order numbers			
Order Number			FLN 6/9

Mechanical data		Type	FLN 6/9
Terminal and mounting			
Terminals			Pins for printed circuit boards
Measures and weights			
Core type			UI 30/10,5
Weight			0.19 kg

