

Low profile transformer



Advantages

- Minimum size at high output
- Low height
- Double input voltage for series or parallel connection
- Double output voltage for series or parallel connection
- Designed for high ambient temperatures
- Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDensiFill resin encapsulation
- Coil shell in 2-chamber technology
- Self-extinguishing potting material


Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As an isolating transformer for the safe electrical isolation of the input and output sides. The transformer may be used to set up protective separation as a protective measure.

As a safety isolating transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

Circuit Diagram



Standards



Safety isolating transformer
to: VDE 0570 Part 2-6, DIN EN 61558-2-6, EN 61558-2-6, IEC 61558-2-6,
UL 5085-1/-2, CSA 22.2 No.66

Approvals



ENEC 10 (VDE), UL 5085-1/-2, CSA 22.2 No.66




Low profile transformer FLN 24/12

Electrical data

| Type | FLN 24/12 |
|---------------------------------|------------------------------|
| Input | |
| Rated input Voltage | 2 x 115 Vac |
| Rated frequency | 50 - 60 Hz |
| Output | |
| Rated output voltage | 2 x 12 Vac |
| Rated Power | 24.0 VA |
| No-load voltage (app. x factor) | 1.26 |
| No-load loss (typ.) | 2.00 W |
| Efficiency | 74 % |
| Standards | |
| Classification | Safety isolating transformer |
| Approvals | |
| Approvals | cURus, ENEC 10 (VDE) |
| Environment | |
| Ambient temperature max. | 70 °C |
| Safety and protection | |
| Type | encapsulated |
| Class of Insulation System | B |
| Protection index | IP 00 |
| Safety class (prepared) | II |
| Short circuit strength | non-short-circuit proof |
| Order numbers | |
| Order Number | FLN 24/12 |

Mechanical data

| Type | FLN 24/12 |
|-----------------------|---------------------------------|
| Terminal and mounting | |
| Terminals | Pins for printed circuit boards |
| Measures and weights | |
| Core type | UI 39/17 |
| Weight | 0.49 kg |



Subjects to change.