

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [39-00-0077](#)  
**Status:** **Active**  
**Overview:** Mini-Fit Jr.™ Power Connectors  
**Description:** Mini-Fit® Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 16 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-5556-001 (PDF)</a>
<a href="#">Product Specification PS-5556-001 (PDF)</a>	<a href="#">Test Summary TS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-5556-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr.™ Power Connectors</a>
Packaging Alternative	<a href="#">39-00-0078 (Loose)</a>
Product Name	Mini-Fit®
UPC	800753627741

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	135.300/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm²	N/A

**Electrical**


Current - Maximum per Contact	9A
Voltage - Maximum	600V

**Material Info**

Old Part Number	5556T3
-----------------	--------

**Reference - Drawing Numbers**

Packaging Specification	PK-5556-001
Product Specification	PS-5556-001, PS-5556-002, RPS-30067-001, RPS-30067-002, RPS-30067-003, RPS-5557-002
Sales Drawing	SD-5556****
Test Summary	TS-5556-002



**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC Contains SVHC: No Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[5556Series](#)

**Mates With**

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

**Use With**

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [5559](#) Mini-Fit Jr.™ Plug Housing, Dual Row

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
FineAdjust™ Applicator for Insulation OD 2.60-3.15mm	<a href="#">0639002800</a>

Optimized for 16 AWG Only Extraction Tool	<u>0011030044</u>
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<u>0638190900</u>
FineAdjust™ Applicator for Insulation OD 2.20-2.45mm	<u>0639003000</u>
Optimized for 16 AWG Only FineAdjust™ Applicator for Insulation OD 1.80-2.20mm	<u>0639015300</u>
Optimized for 16 AWG Only T2 Terminator™ for insulation OD 2.60-3.15mm	<u>0639102800</u>
optimized for 16 AWG only T2 Terminator™ for insulation OD 2.20-2.45mm	<u>0639103000</u>
optimized for 16 AWG only	
<b>Japan</b>	
<b>Description</b>	<b>Product #</b>
Applicator for M21 1A Bench Press, 18-24 AWG Wire	<u>0570223000</u>
Side-Feed Applicator For Full-Auto Machine	<u>0570223200</u>
Hand Extraction Tool	<u>0570316000</u>

This document was generated on 04/03/2014

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**