

LC1D186B7

TeSys D contactor - 3P(3 NO) - AC-3 - ≤ 440 V
18 A - 24 V AC coil



Product availability: Stock - Normally stocked in distribution facility



Main

Commercial Status	Commercialised
Range of product	TeSys D
Product or component type	Contacteur
Device short name	LC1D
Contacteur application	Motor control Resistive load
Utilisation category	AC-1 AC-3
Poles description	3P
Pole contact composition	3 NO
[Ue] rated operational voltage	<= 300 V DC for power circuit <= 690 V AC 25...400 Hz for power circuit
[Ie] rated operational current	18 A (<= 140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit 32 A (<= 140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
Motor power kW	10 kW at 660...690 V AC 50/60 Hz 10 kW at 500 V AC 50/60 Hz 9 kW at 415...440 V AC 50/60 Hz 7.5 kW at 380...400 V AC 50/60 Hz 4 kW at 220...230 V AC 50/60 Hz
Motor power hp	15 hp at 575/600 V AC 50/60 Hz for 3 phases motors 10 hp at 460/480 V AC 50/60 Hz for 3 phases motors 5 hp at 230/240 V AC 50/60 Hz for 3 phases motors 5 hp at 200/208 V AC 50/60 Hz for 3 phases motors 3 hp at 230/240 V AC 50/60 Hz for 1 phase motors 1 hp at 115 V AC 50/60 Hz for 1 phase motors
Control circuit type	AC 50/60 Hz
Control circuit voltage	24 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 1 NC
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Overvoltage category	III
[Ith] conventional free air thermal current	32 A at <= 140 °F (60 °C) for power circuit 10 A at <= 140 °F (60 °C) for signalling circuit
Irms rated making capacity	300 A at 440 V for power circuit conforming to IEC 60947 250 A DC for signalling circuit conforming to IEC 60947-5-1 140 A AC for signalling circuit conforming to IEC 60947-5-1
Rated breaking capacity	300 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	84 A <= 104 °F (40 °C) 1 min power circuit 40 A <= 104 °F (40 °C) 10 min power circuit 240 A <= 104 °F (40 °C) 1 s power circuit 145 A <= 104 °F (40 °C) 10 s power circuit 140 A 100 ms signalling circuit 120 A 500 ms signalling circuit 100 A 1 s signalling circuit
Associated fuse rating	35 A gG at <= 690 V coordination type 2 for power circuit 50 A gG at <= 690 V coordination type 1 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1
Average impedance	2.5 mOhm at 50 Hz - Ith 32 A for power circuit

[Ui] rated insulation voltage	600 V for signalling circuit certifications UL 600 V for signalling circuit certifications CSA 690 V for signalling circuit conforming to IEC 60947-1 600 V for power circuit certifications UL 600 V for power circuit certifications CSA 690 V for power circuit conforming to IEC 60947-4-1
Electrical durability	1 Mcycles 32 A AC-1 at $U_e \leq 440$ V 1.65 Mcycles 18 A AC-3 at $U_e \leq 440$ V
Power dissipation per pole	0.8 W AC-3 2.5 W AC-1
Protective cover	With
Mounting support	Plate Rail
Standards	EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 No 14
Product certifications	BV CCC CSA DNV GL GOST RINA UL LROS
Connections - terminals	Power circuit: lugs-ring terminals - external diameter: 0.31 in (8 mm) Control circuit: lugs-ring terminals - external diameter: 0.31 in (8 mm)
Tightening torque	Power circuit: 15.04 lbf.in (1.7 N.m) - on lugs-ring terminals - with screwdriver Philips No 2 screw : M3.5 Power circuit: 15.04 lbf.in (1.7 N.m) - on lugs-ring terminals - with screwdriver flat \varnothing 8 mm screw : M3.5 Control circuit: 15.04 lbf.in (1.7 N.m) - on lugs-ring terminals - with screwdriver Philips No 2 screw : M3.5 Control circuit: 15.04 lbf.in (1.7 N.m) - on lugs-ring terminals - with screwdriver flat \varnothing 6 mm screw : M3.5
Operating time	4...19 ms opening 12...22 ms closing
Safety reliability level	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
Mechanical durability	15 Mcycles
Operating rate	3600 cyc/h at ≤ 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.85...1.1 U_c at 140 °F (60 °C) operational 60 Hz 0.8...1.1 U_c at 140 °F (60 °C) operational 50 Hz 0.3...0.6 U_c at 140 °F (60 °C) drop-out 50/60 Hz
Inrush power in VA	70 VA at 68 °F (20 °C) ($\cos \phi$ 0.75) 50 Hz 70 VA at 68 °F (20 °C) ($\cos \phi$ 0.75) 60 Hz
Hold-in power consumption in VA	7 VA at 68 °F (20 °C) ($\cos \phi$ 0.3) 50 Hz 7.5 VA at 68 °F (20 °C) ($\cos \phi$ 0.3) 60 Hz
Heat dissipation	2...3 W at 50/60 Hz
Auxiliary contacts type	Type mirror contact (1 NC) conforming to IEC 60947-4-1 Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1
Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit

Non-overlap time	1.5 ms on energisation (between NC and NO contact) 1.5 ms on de-energisation (between NC and NO contact)
Insulation resistance	> 10 MOhm for signalling circuit

Environment

IP degree of protection	IP2x front face conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	23...140 °F (-5...60 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Permissible ambient air temperature around the device	-40...158 °F (-40...70 °C) at Uc
Operating altitude	9842.52 ft (3000 m) without derating in temperature
Fire resistance	1562 °F (850 °C) conforming to IEC 60695-2-1
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 10 Gn for 11 ms Vibrations contactor closed 4 Gn, 5...300 Hz Vibrations contactor open 2 Gn, 5...300 Hz
Height	3.03 in (77 mm)
Width	1.77 in (45 mm)
Depth	3.39 in (86 mm)
Product weight	0.73 lb(US) (0.33 kg)

Ordering and shipping details

Category	22345 - CTR,D-LINE,OPEN,NONREV-NEW
Discount Schedule	I12
GTIN	00785901272564
Nbr. of units in pkg.	1
Package weight(Lbs)	0.79
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0633 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------