

# Key Lock Switch



**S216R**



**S215E-SP**

## Specifications:

Contact Rating	: 4A @ 125V AC, 2A @ 250V AC, 4A @ 28V DC
Maximum Contact Resistance	: 10mΩ
Minimum Insulation Resistance	: 500MΩ (500V DC)
Dielectric Strength	: 1,500V AC at 1 minute
Lock	: Bright Nickel Plated Zinc Alloy with Nickel Facing
Tumbler Mechanism	: 4-Disc Tumbler Cylinder
Keys	: Brass with Code Number
Contacts	: Golden Plated Cu (Q Contact Material)
Terminals	: Golden Plated Cu (Q Contact Material)
Actuator Style	: Flat

## Part Number Table

Description	Contact Configuration	Angle of Throw	No. of Switch Positions	Part Number
Keyswitch, DPST, 3 Pos, MOM, RDM	SPST	45	3	S215E-SP
Keyswitch, DPST, 2 Pos, RDM, 2 Keypull	SPDT	90	2	S216R

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.