


HSMF-C153/C155/C156/C157/C158

Bi-color Surface Mount Chip LEDs



Data Sheet



Description

The HSMF-C15x series of bicolor chip-type LEDs is designed in an industry standard package for ease of handling and use. These bicolor LEDs are available as high efficiency red/yellow, high efficiency red/green, yellow/green, orange/green and green/amber. The HSMF-C15x has the widely used 3.2 x 2.7 mm footprint and wide viewing angle make this LED exceptional for backlighting applications.

All packages are compatible with reflow solder processes. The small size and wide viewing angle make these LEDs prime choices for backlighting applications and front panel indicators especially where space is a premium.

Features

- Small size
- Industry standard footprint
- Compatible with IR solder
- Diffused optics
- Operating temperature range of -40°C to $+85^{\circ}\text{C}$
- Five color combinations available:
Red/Yellow, Red/Green, Yellow/Green, Orange/Green and Green/Amber.
- Available in 8 mm tape on 7 in. (178 mm) diameter reels

Applications

- Push-button backlighting
- Symbol backlighting
- Status indicator
- Front panel indicator


Device Selection Guide

| Part Number | Parts per Reel | Color | Package Description |
|-------------|----------------|-------------------------------|---------------------|
| HSMF-C153 | 3000 | GaP Yellow / GaP HER | Untinted, Diffused |
| HSMF-C155 | 3000 | GaP HER / GaP Green | Untinted, Diffused |
| HSMF-C156 | 3000 | GaP Yellow / GaP Green | Untinted, Diffused |
| HSMF-C157 | 3000 | GaP Orange / GaP Green | Untinted, Diffused |
| HSMF-C158 | 3000 | AllnGaP Green / AllnGap Amber | Untinted, Diffused |


CAUTION: HSMF-C15x LEDs are Class 1A ESD sensitive per JESD22-A114C.01. Please observe appropriate precautions during handling and processing. Refer to Application Note AN-1142 for additional details.

Package Dimensions

CHINA SOURCE



TAIWAN SOURCE



NOTES:

1. ALL DIMENSIONS IN MILLIMETERS (INCHES).
2. TOLERANCE IS ± 0.1 mm (± 0.004 IN.) UNLESS OTHERWISE SPECIFIED.

| POLARITY | HSMF-C153 | HSMF-C155 | HSMF-C156 | HSMF-C157 | HSMF-C158 |
|----------|-----------|-----------|-----------|-----------|-----------|
| ① — >— ② | Yellow | Green | Green | Green | Green |
| ③ — >— ④ | HER | HER | Yellow | Orange | Amber |

Absolute Maximum Ratings at $T_A = 25^\circ\text{C}$

| Parameter | GaP | AllnGaP Green | AllnGaP Amber | Units |
|--|---|---------------|---------------|------------------|
| DC Forward Current ^[1] | 20 | 20 | 25 | mA |
| Power Dissipation ^[2] | 65 | 52 | 60 | mW |
| Reverse Voltage ($I_R = 100\mu\text{A}$) | 5 | 5 | 5 | V |
| LED Junction Temperature | 95 | 95 | 95 | $^\circ\text{C}$ |
| Operating Temperature Range | -40 to 85 $^\circ\text{C}$ | | | |
| Storage Temperature Range | -40 to 85 $^\circ\text{C}$ | | | |
| Soldering Temperature | See reflow soldering profile (Figure 6 & 7) | | | |

Notes:

1. Derate linearly as shown in Figure 4 for temperature above 25 $^\circ\text{C}$.
2. Pulse condition of 1/10 duty and 0.1 msec. width.

Optical Characteristics at $T_A = 25^\circ\text{C}$

| Part Number | Luminous Intensity I_V ^[1] (mcd) @ 20mA | | Color, Peak Wavelength λ_d (nm) Typical | Color, Dominant Wavelength λ_d ^[2] (nm) Typical | Viewing Angle $2\theta_{1/2}$ ^[3] (Degrees) Typical |
|---------------|--|------|--|---|---|
| | Min. | Typ. | | | |
| GaP HER | 2.50 | 10.0 | 630 | 626 | 170 |
| GaP Yellow | 2.50 | 8.0 | 589 | 586 | 170 |
| GaP Green | 4.00 | 15.0 | 570 | 572 | 170 |
| GaP Orange | 2.50 | 8.0 | 605 | 604 | 170 |
| AllnGaP Green | 28.50 | 45.0 | 570 | 572 | 170 |
| AllnGaP Amber | 28.50 | 55.0 | 595 | 592 | 170 |

Notes:

1. The luminous intensity I_V is measured at the peak of the spatial radiation pattern which may not be aligned with the mechanical axis of the LED package.
2. The dominant wavelength, λ_d , is derived from the CIE Chromaticity Diagram and represents the perceived color of the device.
3. $\lambda_{1/2}$ is the off-axis angle where the luminous intensity is 1/2 the peak intensity.

Electrical Characteristics at $T_A = 25^\circ\text{C}$

| Part Number | Forward Voltage V_F (Volts) ^[1] @ $I_F = 20\text{mA}$ | | Reverse Breakdown VR (Volts) @ $I_R =$ 100 μA | Capacitance C (pF) @ $V_F = 0, f = 1\text{Mhz}$ | Thermal Resistance $R_{\theta J-P}$ ($^\circ\text{C}/\text{W}$) |
|---------------|--|------|--|--|--|
| | Typ. | Max. | Min. | Typ. | Typ. |
| GaP HER | 2.1 | 2.6 | 5 | 5 | 325 |
| GaP Yellow | 2.1 | 2.6 | 5 | 6 | 325 |
| GaP Green | 2.2 | 2.6 | 5 | 9 | 325 |
| GaP Orange | 2.2 | 2.6 | 5 | 7 | 325 |
| AllnGaP Green | 2.1 | 2.4 | 5 | 22 | 325 |
| AllnGaP Amber | 1.9 | 2.4 | 5 | 45 | 325 |

Notes: The bicolor package contain two individual light sources of different color. The specifications above refer to each color of a particular package.

Color Bin Limits

GaP HER Color Bins ^[1]

| Bin ID | Dominant Wavelength (nm) | |
|--------|--------------------------|---------|
| | Minimum | Maximum |
| - | 620.0 | 635.0 |

Tolerance : ± 1 nm

GaP Yellow / AlInGaP Amber Color Bins ^[1]

| Bin ID | Dominant Wavelength (nm) | |
|--------|--------------------------|---------|
| | Minimum | Maximum |
| A | 582.0 | 584.5 |
| B | 584.5 | 587.0 |
| C | 587.0 | 589.5 |
| D | 589.5 | 592.0 |
| E | 592.0 | 594.5 |
| F | 594.5 | 597.0 |

Tolerance : ± 1 nm

GaP Orange Color Bins ^[1]

| Bin ID | Dominant Wavelength (nm) | |
|--------|--------------------------|---------|
| | Minimum | Maximum |
| A | 597.0 | 600.0 |
| B | 600.0 | 603.0 |
| C | 603.0 | 606.0 |
| D | 606.0 | 609.0 |
| E | 609.0 | 612.0 |
| F | 612.0 | 615.0 |

Tolerance : ± 1 nm

GaP Green Color Bins ^[1]

| Bin ID | Dominant Wavelength (nm) | |
|--------|--------------------------|---------|
| | Minimum | Maximum |
| A | 561.5 | 564.5 |
| B | 564.5 | 567.5 |
| C | 567.5 | 570.5 |
| D | 570.5 | 573.5 |
| E | 573.5 | 576.5 |

Tolerance : ± 1 nm

AllnGaP Green Color Bins ^[1]

| Bin ID | Dominant Wavelength (nm) | |
|--------|--------------------------|---------|
| | Minimum | Maximum |
| A | 561.5 | 564.5 |
| B | 564.5 | 567.5 |
| C | 567.5 | 570.5 |
| D | 570.5 | 573.5 |
| E | 573.5 | 576.5 |

Tolerance : ± 1 nm

Light Intensity (Iv) Bin Limits^[1]

| Intensity (mcd) | | |
|-----------------|-------|-------|
| Bin ID | Min. | Max. |
| A | 0.11 | 0.18 |
| B | 0.18 | 0.29 |
| C | 0.29 | 0.45 |
| D | 0.45 | 0.72 |
| E | 0.72 | 1.10 |
| F | 1.10 | 1.80 |
| G | 1.80 | 2.80 |
| H | 2.80 | 4.50 |
| J | 4.50 | 7.20 |
| K | 7.20 | 11.20 |
| L | 11.20 | 18.00 |
| M | 18.00 | 28.50 |

| Intensity (mcd) | | |
|-----------------|---------|---------|
| Bin ID | Min. | Max. |
| N | 28.50 | 45.00 |
| P | 45.00 | 71.50 |
| Q | 71.50 | 112.50 |
| R | 112.50 | 180.00 |
| S | 180.00 | 285.00 |
| T | 285.00 | 450.00 |
| U | 450.00 | 715.00 |
| V | 715.00 | 1125.00 |
| W | 1125.00 | 1800.00 |
| X | 1800.00 | 2850.00 |
| Y | 2850.00 | 4500.00 |

Tolerance: $\pm 15\%$.

Note:

1. Bin categories are established for classification of products. Products may not be available in all categories. Please contact your Avago representative for information on currently available bins.




Figure 1. Relative intensity vs. wavelength.




Figure 2. Forward current vs. forward voltage.




Figure 3. Luminous intensity vs. forward current (all colors).




Figure 4. Maximum forward current vs. ambient temperature.




Figure 5. Relative intensity vs. angle for HSMF-C153, C155, C156, C157 and C158.




Figure 6. Recommended reflow soldering profile.





Figure 7. Recommended Pb free reflow soldering profile.



Note: 1. All dimensions in millimeters (inches).

Figure 8. Recommended solder pad pattern.





Figure 9. Reeling orientation.



Note:
All dimensions in millimeters (inches).

Figure 10. Reel dimensions.




TABLE 1
DIMENSIONS IN MILLIMETERS (INCHES)

| PART NUMBER | DIM. A ± 0.10 (0.004) | DIM. B ± 0.10 (0.004) | DIM. C ± 0.10 (0.004) |
|------------------|--------------------------|--------------------------|--------------------------|
| HSMF-C15x SERIES | 3.52 (0.139) | 3.02 (0.119) | 1.40 (0.055) |

Figure 11. Tape dimensions.




Figure 12. Tape leader and trailer dimensions.

Notes:

1. All dimensions in millimeters (inches).
2. Tolerance is ±0.1 mm (±0.004 in.) unless otherwise specified.

Convective IR Reflow Soldering

For more information on IR reflow soldering, refer to Application Note 1060, *Surface Mounting SMT LED Indicator Components*.

Storage Condition:
5 to 30°C @ 60% RH max.

Baking is required under the condition:

- a) Humidity Indicator Card is >10% when read at 23 ± 5°C
- b) Device exposed to factory conditions < 30°C/60% RH more than 672 hours.

Baking recommended condition:
60 ± 5°C for 20 hours.

For product information and a complete list of distributors, please go to our website: www.avagotech.com

