

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [02-06-5103](#)
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	1561
Application	Power
Crimp Quality Equipment	Yes
Overview	Standard .062" Pin and Socket Power Connectors
Packaging Alternative	02-06-5100 (Reel)
Product Name	Standard .062"
UPC	800753618763

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.080/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm ²	N/A

Material Info

Old Part Number 1561-(P550)L

Reference - Drawing Numbers

Sales Drawing SD-1561-*




image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

1561Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Standard 1.57mm Pin and Socket Crimp Terminals, 18-24 AWG	0638191300
Hand Crimper - DISTRIBUTION ONLY	0638111000
Hand Insertion Tool	0011020001
Manual Extraction Tool	0011030002

This document was generated on 05/23/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION