


HONEYWELL
PART NUMBER

411SM1

PRODUCT CODE
TZG0011

REV	DOCUMENT	CHANGED BY	CHECK
8	0038115	VS 28APR08	BLR



NOTE -

- 1-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
- 2-TERMINALS ARE PLATED FOR SOLDERING
- 3-SWITCH WILL WITHSTAND TEMPERATURES FROM -40° TO +250° F
- 4-TEMPERATURE EXTREMES MAY CAUSE FORCE CHARACTERISTICS TO CHANGE. STATED CHARACTERISTICS ARE FOR ROOM TEMPERATURE
- 5-SEAL CONSTRUCTION PROVIDES SPLASH AND DUST RESISTANCE

RELEASE NO.
PR - 1539 -T

REPLACES
-

CHARACTERISTICS 4

OPERATING FORCE - - 3 - 7 1/2 OZ

RELEASE FORCE - - - - 1 OZ MIN

DIFFERENTIAL TRAVEL - - .004 MAX

OVERTRAVEL - - - - .005 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT S P D T			
30 VOLTS DC RATING			
		SEA LEVEL	50,000 FT
INDUCTIVE		3 AMP	2.5 AMP
RESISTIVE		5 AMP	5 AMP
MAXIMUM INRUSH 24 AMP			
APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4	 
	UL, CSA	5A, <u>250</u> VAC	  BRAND L4

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE X ±

ONE PLACE .X ±

TWO PLACE .XX ±

THREE PLACE .XXX ±

FOUR PLACE .XXXX ±

ANGLES ±

0.030

0.015

0.005

THIRD ANGLE PROJECTION



DRAWN	VK	04 DEC 07
CHECK	RJ	04 DEC 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

HoneywellTITLE
SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
B	I	411SM1	8
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1