

## HDC insert HDC HD 8 MC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The HD range features a high density of contacts. It is thus optimally suited for signal processing.  
 The wire connection level is designed as a crimp contact. The established crimp connection has been used as a standard for decades.  
 Crimp contacts are not delivered with the inserts.  
 Number of poles: **7 - 8**  
 Rated current: **10 A**  
 Rated voltage: **42/250 V**  
 Nominal voltage acc. to UL/CSA: **600 V AC/DC**  
 Crimp connection

### General ordering data

Type	HDC HD 8 MC
Order No.	<a href="#">1650590000</a>
Version	HDC insert, Male, 50 V, 10 A, No. of poles: 8, Crimp connection, Size: 1
GTIN (EAN)	4008190299262
Qty.	1 pc(s).

**HDC insert  
HDC HD 8 MC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	21 mm	Width	21 mm
Height	34 mm	Net weight	10 g

**Dimensions**

Height of plug	34 mm	Total length base	21 mm
----------------	-------	-------------------	-------

**General data**

Size	1	Series	HD
Rated voltage (DIN EN 61984)	50 V	Rated voltage according to UL/CSA	600 V AC/DC
Rated impulse voltage (DIN EN 61984)	4 kV	Rated current (DIN EN 61984)	10 A
UL 94 flammability rating	V-0	Insulating material group	IIIa
Insulation resistance	10 <sup>10</sup> Ω	Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)
Conductor cross-section	2.5 mm <sup>2</sup>	No. of poles	8
Plugging cycles, silver	≥ 500	Plugging cycles, gold	≥ 500
Pollution severity	3	Type	Male

**Connection data PE**

Wire connection cross-section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>
Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max.	2.5 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 14
Wire cross-section, solid, min.	0.5 mm <sup>2</sup>	Wire cross-section, solid, max.	2.5 mm <sup>2</sup>
Rated cross-section	2.5 mm <sup>2</sup>		

**Rating data**

Rated current (DIN EN 61984)	10 A	Rated impulse voltage (DIN EN 61984)	4 kV
Rated voltage (DIN EN 61984)	50 V	Rated voltage according to UL/CSA	600 V AC/DC

**Version**

Wire connection cross section AWG, min.	AWG 26	Wire connection cross section AWG, max.	AWG 14
Stripping length, rated connection	8 mm	Type of connection	Crimp connection
Size	1	Volume resistance	≤ 4mΩ
Surface finish	Silver passivated, gold	Material	Copper alloy

**Classifications**

ETIM 3.0	EC001121	UNSPSC	30-21-18-01
eClass 5.1	27-14-34-19	eClass 6.2	27-26-12-04
eClass 7.1	27-44-02-05		

**Data sheet****HDC insert  
HDC HD 8 MC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Product information**

Descriptive text ordering data	Reduce the voltage to 42 V when using metal housings
Descriptive text technical data	HD 8 insert without protective earth connection
Descriptive text accessories	Accessories, see chapter J - Tools, see chapter K

**Approvals**

Approvals



ROHS

Conform

**Data sheet****HDC insert  
HDC HD 8 MC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**