

## Housing/Lens Assemblies

## T-2 Indicator Cartridge Lamps

Line No.	Lamp No.	Design Volts	Design Amps	Design Watts	Filament Type	Average End Foot Candles	Rated Life
1	918IC <sup>1</sup>	12	0.04	0.48	C-2V	550	10,000
2	926IC <sup>1</sup>	16	0.04	0.64	C-2F	750	7,500
3	933IC <sup>1</sup>	24	0.017	0.42	C-2F	200	15,000
4	934IC <sup>1</sup>	24	0.04	0.96	C-2F	650	8,000
5	938IC <sup>1</sup>	28	0.04	1.12	C-2F	1500	6,000
6	941IC <sup>1</sup>	48	0.04	1.92	C-2F	3000	5,000

1 C14C-0001-0001

### Lenses

Line No	Color	Part Number	
		Transparent	Translucent
1	Amber	30140	-
2	Clear	30141	-
3	Red	30142	30147
4	Blue	30143	-
5	Green	30144	30149
6	Yellow	-	30145
7	White	-	30146



### Indicator Sockets

Line No	PartNo	Alternate No.	Base
1	SM1A*	30098	Solder Lugs



\*MIL - Std. 18235 MIL-L-3661 A-MIL Std. 202B  
 Material: Black Phenolic  
 Max. Current - 1 amp.

#30098 Socket

### Dimensions

Lenses : Diameter : 0.400"; Height : 0.425"  
 Socket : Front of panel to end of terminals: 1.0"  
 Mounting Hole : 0.372" diameter

## Housing/Lens Assemblies

## T-2 Pilot Cartridge Lamps

Line No.	Lamp No.	Design Volts	Design Amps	Design Watts	Filament Type	Average End Foot Candles	Rated Life
1	12PC <sup>1</sup>	12	0.17	2	C-2F	2400	12,000
2	24PC <sup>1</sup>	24	0.073	0.17	C-2F	3000	10,000
3	28PC <sup>1</sup>	28	0.04	1.1	C-2F	1500	5,000
4	120PC <sup>2</sup>	120	0.025	3	CC-7A	1000	7,500

1 C14C-0027-0002

2 C14C-0027-0001

\*Conforms to MiL - Std. 18238-2  
MOL=1.125" (excluding pins)



### Lenses

Line No	Color	Part Number	
		Transparent	Translucent
1	Amber	30140	-
2	Clear	30141	-
3	Red	30142	30147
4	Blue	30143	-
5	Green	30144	30149
6	Yellow	-	30145
7	White	-	30146



### Indicator Sockets

Line No	PartNo	Alternate No.	Base
1	SM2A*	30096	Solder Lugs



\*MiL - Std. 18235 MiL-L-3661 A-MiL Std. 202B  
Material: Black Phenolic  
Max. Current - 1 amp.

#30096 Socket

### Dimensions

Lenses : Diameter : 0.400"; Height : 0.425"  
Socket : Front of panel to end of terminals: 1.0"  
Mounting Hole : 0.372" diameter