

DV5200 Series

Tubeaxial

127x127x38mm

- DC fans with electronically commutated external rotor motor. Fully integrated commutation electronics. With electronic protection against reverse polarity, blocking and overloading.

-

- Mounting from either face using four 4.3 mm holes.

- Air exhaust over struts. Rotational direction CCW looking at rotor.

- Electrical connection via leads AWG 22, TR 64. Stripped and tinned ends. Housing ground lug for screw M4 x 8 (TORX).

- UL, CSA, VDE approvals on most models, please contact application engineering.

DV5212N	1	158.9	12	9 to 15	21	56	65	Ball	5000
DV5214N	1	158.9	24	16 to 30	21	56	65	Ball	5000
DV5218N	1	158.9	48	36 to 60	21	56	65	Ball	5000

