


**P-series  
PDU 16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Turn five into three – that's the winning formula of the new P series with the PUSH IN connection system in which the pitches for 2.5, 4, 6 and 10 mm<sup>2</sup> are each combined in one terminal block. That means you now need only three rows of terminals for wiring five pitches up to 16 mm<sup>2</sup>.

This innovative concept unites the efficiency of the wide pitch with the compactness of the narrow one. The result is a maximum rated current and minimum size at the same time. That eases the workload in purchasing, logistics and design.

**General ordering data**

Type	PDU 16
Order No.	<a href="#">1896400000</a>
Version	P-series, Feed-through terminal, Rated cross-section: 16 mm <sup>2</sup> , PUSH IN, Direct mounting
GTIN (EAN)	4032248511518
Qty.	25 pc(s).

## P-series PDU 16

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	12.1 mm	Height	80.5 mm
Height of lowest version	48 mm	Depth	47.5 mm
Net weight	36.68 g		

### Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

### Rated data IECEx/ATEX

Certificate No. (ATEX)	KEMA06ATEX0177U	ATEX certificate	IECEXKEM06.0032U
ATEX certificate	KEMA06ATEX0177U_e.pdf	Certificate No. (IECEX)	IECEXKEM06.0032U
IEC Ex certificate	IECEXKEM06.0032U_e.pdf	Max. voltage (ATEX)	550 V
Current (ATEX)	59 A	Wire cross section max. (ATEX)	16 mm <sup>2</sup>
Max. voltage (IECEX)	550 V	Current (IECEX)	59 A
Wire cross section max. (IECEX)	16 mm <sup>2</sup>	Voltage, cross-connection	CrossConnectionGuide.pdf
Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity	Marking EN 60079-7	
Marking ATEX Directive 94/9/EC	II 2 G D		Ex e II

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Open sides	right	Type of mounting	Snap-on
Version	PUSH IN connection, for plug-in cross-connector, One end without connector		

### CSA ratings data

Certificate No. (CSA)	200039-1751332	Voltage size B (CSA)	600 V
Voltage size C (CSA)	600 V	Current size B (CSA)	78 A
Current size C (CSA)	78 A	Wire cross section max. (CSA)	4 AWG
Wire cross section min. (CSA)	14 AWG		

**P-series  
PDU 16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Clampable wires (rated connection)**

Type of connection	PUSH IN	Stripping length	18 mm
Blade size	1.0 x 5.5 mm	Connection direction	top
Number of connections	2	Clamping range, rated connection, min.	2.5 mm <sup>2</sup>
Clamping range, rated connection, max.	16 mm <sup>2</sup>	Gauge to IEC 60947-1	B6
Wire connection cross section, solid core, min. rated connection	2.5 mm <sup>2</sup>	Wire connection cross section, solid core max. rated connection	16 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	16 mm <sup>2</sup>	Wire connection cross-section, finely stranded, min.	2.5 mm <sup>2</sup>
Finely stranded, max. (rated connection)	16 mm <sup>2</sup>	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	2.5 mm <sup>2</sup>
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	16 mm <sup>2</sup>	Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min.	2.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max.	16 mm <sup>2</sup>		

**Rated data**

Rated cross-section	16 mm <sup>2</sup>	Rated voltage	800 V
Rated impulse withstand voltage	8 kV	Rated current	76 A
Pollution severity	3		

**UL ratings data**

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	4 AWG
Conductor size Factory wiring min. (cURus)	14 AWG	Conductor size Field wiring max. (cURus)	4 AWG
Conductor size Field wiring min. (cURus)	14 AWG	Current size B (cURus)	75 A
Current size C (cURus)	75 A	Voltage size B (cURus)	600 V
Voltage size C (cURus)	600 V		

**Material data**

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

**System specifications**

Product family	P-series	Type of connection	PUSH IN
Connection direction	top	Number of levels	1
Number of connections	2	No. of clamping points per level	2
Levels cross-connected internally	No	Mounting rail	TS 35
End cover plate required	Yes		

**Classifications**

ETIM 3.0	EC000897	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-20	eClass 6.2	27-14-11-20
eClass 7.1	27-14-11-20		

**Data sheet**

**P-series  
PDU 16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS

Conform

**Data sheet**

**P-series  
PDU 16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

