


High Voltage Brushless DC Blowers

5.7" (145mm) BLDC Bypass Blower

400 Watt, 240 Volt Standard Flow



Specification	Units	Part/ Model Number					
		117634	117640	117633	117639	117632	117638
Stages	-	1	1	2	2	3	3
Max Sealed Vacuum	in. H2O	28	28	45	45	60	60
	mbar	69.7	69.7	112.1	112.1	149.5	149.5
Max Sealed Pressure	in. H2O	30	30	51	51	72	72
	mbar	74.7	74.7	127	127	179.4	179.4
Max Flow Rate	CFM	70	70	67	67	65	65
	m3/hr	119	119	113.9	113.9	110.5	110.5
Length (I)	Inches	2.53	2.53	1.25	1.25	2.14	2.14
	mm	64.3	64.3	31.8	31.8	54.4	54.4
Length (L)	Inches	5.08	5.08	5.99	5.99	6.89	6.89
	mm	129	129	152.1	152.1	175	175
Speed Control	-	Mechanical	Electrical	Mechanical	Electrical	Mechanical	Electrical




Notes:

- Input Voltage Range:** 216-264 Volts AC RMS, 50/60 Hz., Single Phase.
- Input Current:** 5 amps AC RMS
- Operating Temperature (Ambient Air and Working Air):** 0° C to 50° C
- Storage Temperature:** -40° C to 85° C
- Dielectric Testing:** 1800 Volts AC RMS 60 Hz applied for one second between input pins and ground, 3mA leakage maximum.
- Speed Control:** E (Electrical) Pulse Width Modification or Analog input voltage (user supplied), 0 to 10 Volts DC, 10mA maximum, 3 to 15 Volts DC. Access to sensitivity adjustment for 0 to 10 VDC speed control. (Ref. pin connection).
M (Mechanical): A potentiometer is available for speed control of the blower. The potentiometer can be preset for a specific speed. Access for speed adjustment located in blower housing.
- Approximate Weight:** 6 Lbs. / 2.2 Kg.
- Regulatory Agency Certification:** Underwriters Laboratories, Inc. qualified per UL507 under File E-94403. Canadian Standards Association qualified per C22.2#113 under File LR 43448.
- Miscellaneous:** Intake and exhaust tubes, all cooling ducts and vents must not be obstructed. Intake and exhaust must be free of grease, oil and foreign particles. Amp housing 350809-1 with sockets for 18 awg lead wire (supplied by customer) mates with post header assembly. Mating harness available upon request. Optional IntelliGen™ controller available for customized performance and features including; tachometer output card; Universal AC input (100V-240V).

This document is for informational purposes only and should not be considered as a binding description of the products or their performance in all applications. The performance data on this page depicts typical performance under controlled laboratory conditions. AMETEK is not responsible for blowers driven beyond factory specified speed, temperature, pressure, flow or without proper alignment. Actual performance will vary depending on the operating environment and application. AMETEK products are not designed for and should not be used in medical life support applications. AMETEK reserves the right to revise its products without notification. The above characteristics represent standard products. For product designed to meet specific applications, contact AMETEK Technical & Industrial Products Sales department.

Typical Performance



Data presented represents blower performance at STANDARD AIR DENSITY, WHICH IS: .075 lb./ft³ (29.92" Hg, Sea Level, 68° F). Vacuum performance available upon request.

This document is for informational purposes only and should not be considered as a binding description of the products or their performance in all applications. The performance data on this page depicts typical performance under controlled laboratory conditions. AMETEK is not responsible for blowers driven beyond factory specified speed, temperature, pressure, flow or without proper alignment. Actual performance will vary depending on the operating environment and application. AMETEK products are not designed for and should not be used in medical life support applications. AMETEK reserves the right to revise its products without notification. The above characteristics represent standard products. For product designed to meet specific applications, contact AMETEK Technical & Industrial Products Sales department.