

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [09-50-3031](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 3 Circuits](#)

Documents:

| | |
|--|---|
| 3D Model | Packaging Specification PK-2139-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-08-50 (PDF) | |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|---|
| Product Family | Crimp Housings |
| Series | 2139 |
| Application | Power, Wire-to-Board |
| MolexKits | Yes |
| Overview | KK® Interconnect System - Molex |
| Product Name | KK® 396 |
| UPC | 800753614017 |

Physical

| | |
|-------------------------------|---------------------------|
| Circuits (maximum) | 3 |
| Color - Resin | Natural |
| Flammability | 94V-2 |
| Gender | Female |
| Glow-Wire Compliant | No |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 0.784/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 3.96mm |
| Temperature Range - Operating | See Product Specification |

Material Info

| | |
|-----------------|---------|
| Old Part Number | 2139-3A |
|-----------------|---------|

Reference - Drawing Numbers

| | |
|-------------------------|-------------|
| Packaging Specification | PK-2139-001 |
| Product Specification | PS-08-50 |
| Sales Drawing | SD-2139 |




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[2139Series](#)

Use With

[2478 Crimp Terminals for 18-24 AWG](#), [2578
Crimp Terminals for 22-26 AWG](#)