

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39-00-0213](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: Mini-Fit® Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel

Documents:

Drawing (PDF)	Packaging Specification PK-5556-001 (PDF)
Product Specification PS-5556-001 (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-5556-002 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit®
UPC	800754319577

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.140/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5556-PBSP
-----------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-5556-001
Product Specification	PS-5556-001, PS-5556-002
Sales Drawing	SD-5556-SP*
Test Summary	TS-5556-002



EU RoHS

**ELV and RoHS
Compliant**

**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[5556Series](#)

Mates With

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

Use With

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [5559](#) Mini-Fit Jr.™ Plug Housing, Dual Row

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	0638190900

FineAdjust™ Applicator for Insulation OD 1.65-2.05mm - 18-24 AWG	<u>0639002900</u>
FineAdjust™ Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639015600</u>
FineAdjust™ Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	<u>0639024800</u>
FineAdjust™ Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639024900</u>
T2 Terminator™ for insulation OD 2.50-2.95mm - 18-24 AWG	<u>0639102600</u>
T2 Terminator™ for insulation OD 1.65 – 2.05mm – 18 – 24 AWG	<u>0639102900</u>
T2 Terminator™ for insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639115600</u>
T2 Terminator™ for insulation OD 1.40-1.70mm - 18-24 AWG	<u>0639123900</u>
T2 Terminator™ for insulation OD 2.50-2.95mm optimized for 18 AWG only	<u>0639124800</u>
T2 Terminator™ for insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639124900</u>
FineAdjust™ Applicator for Insulation OD 2.50-2.95mm - 18-24 AWG	<u>0639002600</u>
FineAdjust™ Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG	<u>0639023900</u>
Extraction Tool	<u>0011030044</u>

This document was generated on 05/07/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION