Advantages of a Finger-Safe, Ice Cube Socket System

The Complete System Solution!



- Offers a "one stop solution" for your power management system.
- Variety of contact configurations and materials to meet your switching needs.
- Plug-In switching capabilities from 10mA to 20 Amps.
- A variety of Feature Codes and operation combinations available for all budgets.
- Ejector clips, ribbed relay housings and space-saving sockets allow for easy removal from crowded DIN rails.
- Color and appearance designed for high visibility in all environments.
- Wiring diagrams include NEMA and IEC standards.
- Engineering availability allows for customized relay solutions.
- Internal Coil Bus Jumper System reduces the number of wires required for hook-up to adjacent sockets.



I.D. Tag/Write-On Plastic Label Used for Custom Identification of Circuits.

Isolated Input and Output Terminals Separates Control Circuits from Load Circuits.

> Slim Design Minimizes Space on DIN Rail.

Mating Hold-Down Clips Available Secures Relay to Socket.



DIN Rail End Clip

Locking Screw Keeps a Snug DIN Rail System by Eliminating Sliding Sockets.

DIN Rail

35 mm Extruded Aluminum Rail. Designed to Work With Most Sockets. Pre-punched for Quick Installation.



Modules Allows for Optional Protection or LED Modules to be Used With Sockets.

0

10-BSNN-


The 700 series sockets have the perfect mix of historical Magnecraft socket quality combined with a dynamic arsenal of options. When mated with the Magnecraft relays and accessories, these RoHS compliant sockets provide a complete modular system that will meet all your plug-in relay requirements in a package that is both visually appealing and functionally outstanding resulting in a Complete Solution.

> **Finger-Safe** Protects Operators from Live Circuits.

Internal Coil Bus Jumper System Allows Connection to Adjacent Sockets Without Additional Wiring.

2-Way Side or DIN Rail Mounting System Retrofits Existing Panel Mounting and 35 mm DIN Rail. **I.D. Tag/Write-On Plastic Label** Used for Identification of Relays in Multi-Relay Circuits.

70-782E14-1 Socket/10 Amp Rating, 300 Volts





BOLD-FACED PART NUMBERS ARE NORMALLY STOCKED ndard Part Number Descriptio

		Standard Part Number	Description
UL Recognized File No. E70550 40787		70-782E14-1	14-Pin Economy, Ice Cube, DIN/Panel Mount with Rising Elevator Box Terminals, Module Compatible
General Specifications (UL 50	8)		·
Characteristics	Units	Value	
Number of Terminals		14	
Electrical Rating			
Nominal Voltage Rating	Volts	300	
Nominal Current Rating	Amps	10	
3	'		
Dielectric Strength			
Output to Adjacent Output Terminals	V rms	3000	
Output to Input Terminals	V rms	3000	
Terminals to Rail / Chassis	V rms	3000	
Temperature			
Operating Range:	°C	- 40 to + 80	
Storage Range:	°C	- 40 to + 105	
Construction	511 (0500	15.00	
Protection Category (Finger-Safe)	EN 60529		
Internal Metal Tracks		Copper Alloy, Zinc Plated	
Screw Terminals		Steel, Zinc Plated	
Screw Style		Combination Head,	
Screw size	mm	M3	
Screw Torque 3.5 mm (Maximum)	Lb-in / Nm	7 / 0.8	
Miscellaneous			
		Din / Panel	
Socket Mounting:	EN 60204-1	AWG mm2	
Wire Size Capacity (Maximum) Soild Cu	AWG, mm2	16 / 18 (2) 1.5 /0.75 (2)	
Stranded Cu	AWG, mm2	16 / 18 (2) 1.5 / 0.75 (2)	
Wire Connection Method		Elevator	
DIN Rail Mounting	EN 60715	35mm	
Chassis Mount Screw Torque	Lb-in / Nm	7 / 0.8	
Flamability Rating	Class	94V-0	
Body Color	0033	Light Gray	
DIN Locking Method		Metal Compression Spring	
Product Certification		UL, CSA	
Conformance		CE, RoHS	
Weight	grams	56	
	3		

Optional Mating Accessories

