



DELIVERED ON A PALLET 

PRODUCT INFORMATION

This symbol appears next to products that can only be delivered on a pallet. Prior to purchase, please ensure you have adequate facilities to unload palletized deliveries. Deliveries can be arranged using specialised transport, but this will incur additional delivery costs.

SAFETY INFORMATION

All our pillar drills are supplied with chuck guards. Premises covered by the Health and Safety at Work Act must have chuck guards fitted as standard equipment.

PILLAR DRILLS



1 D13/5D

350W 230V 5 speed Hobby Bench Drill

No-volt switch

Five speed bench drill complete with 13mm capacity chuck ideally suited for the DIY and hobby user alike. Fan-cooled induction motor. Square table with a rise and fall adjustment featuring a 0-45° tilt, left and right for ease of use. Fitted with a cable and approved plug. Display packed on pallet.

Specification:	
Drilling capacity	... 13mm
Chuck capacity	... 1.5-13mm
Collar diameter	... 40mm
Spindle taper	... 5 (600-2650)
Swing	... 208mm
Spindle travel	... 50mm
Column diameter	... 46mm
Table size	... 160 x 160mm square
Throat depth	... 100mm
Height	... 585mm
Weight	... 18kg

Stock No.	Description
08657	Drill
65961	40mm
65969	JT33/13mm



DELIVERED ON A PALLET 

2 GD13/5C

250W 230V 5 Speed Bench Drill

VDE no-volt switch

General purpose five speed bench drill complete with 13mm capacity chuck ideally suited for the home workshop. It offers a fan cooled motor, depth gauge, a circular tilting table with a rise and fall rack and pinion. Fitted with a cable and approved plug. Display packed on pallet.

Specification:	
Drilling capacity	... 13mm
Chuck capacity	... 13mm
Collar diameter	... 55mm
Spindle taper	... J33
Speeds (r/min)	... 5 (600-2800)
Swing	... 264mm
Spindle travel	... 65mm
Column diameter	... 60mm
Table diameter	... 250mm
Throat depth	... 160mm
Base size	... 205 x 345mm
Height	... 740mm
Weight	... 35kg

Stock No.	Description
65028	Drill
65963	Chuck Guard
65971	J33 Geared Chuck



RADIAL HEAD DRILL

TILTING HEAD

DELIVERED ON A PALLET 

3 GD16/5CFR

370W 230V 5 Speed Floor Standing Radial Drill

VDE no-volt switch

5 speed floor mounted drill complete with 16mm capacity chuck ideal for the maintenance workshop. The radial head allows the drill to be adjusted to any position where space is limited. Powered by a 370W motor offering highly efficient smooth running, it has an adjustable tilting table complete with a rise and fall rack and pinion. Fitted with a cable and approved plug. Carton packed on pallet.

Specification:	
Drilling capacity	... 16mm
Chuck capacity	... 3-16mm
Collar diameter	... 60mm
Spindle taper	... MT2
Speeds (r/min)	... 5 (460-2890)
Swing (radial)	... 840mm
Horizontal arm travel	... 320mm
Spindle travel	... 80mm
Column diameter	... 70mm
Table size	... 260 x 260mm
Throat depth	... 380mm
Base size	... 420 x 250mm
Height	... 1630mm
Weight	... 65kg

Stock No.	Description
43377	Drill
65964	Chuck Guard
45011	MT2 Geared Chuck