### **PRODUCT INFORMATION**

## tesa 62932 Constructive d/s mounting foam tape

#### tesa 62932 foam tape offers an ex- High ultimate adhesive strength **Product** cellent long term adhesive performfor secure bonding performance Description/ ance for demanding constructive ap- High foam elasticity to level-out Application: plications at a small design gap. different thermal expansion of bonded parts Due to its state-of-the-art product de- Very good humidity resistance sign tesa 62932 offers benefits for · Good dampening properties ofvarious industrial applications: fer shock absorption during Thin foam backing allows to impletransport and in daily use ment a small design gap Typical application examples High immediate bonding strength Decorative aluminium cover for fast and reliable assembly even screens on brown goods at low pressure Highly conformable foam backing Door handles in kitchen furniture compensates for design tolerances Moulded decorative profiles for re-٠ or uneven surfaces frigerators or freezers Glass and mirror panels

Product Design:	Backing	Adhesive	Thickness*	Colour
	PE foam	Tackified acrylic	500 µm	Black / white

#### Liner:

Colour	Туре	Thickness*	Weight*
Brown	Glassine paper	71 µm	80 g/m²
Blue	PE	100 µm	94 g/m²

\* Mean values / parameter of the specification

### Dimensions:

Pancake rolls, log rolls, cross wound spools

tesa AG P.O. Box 57 02 62 D- 22771 Hamburg Telephone +49-40 49092618 Telefax +49-40 49094506 tesa self-adhesive tapes are used successfully in many sectors to solve a variety of problems. Our publications contain n umerous examples of such uses, intended to help towards a solution of your particular problems. Each tesa product has been developed for a particular range of applications. Nevertheless, experience has shown that even for one and the same obje ctive, the exact requirements may differ from case to case. We, therefore, recommend that you carry out your own tests in each case, to confirm that the tesa self-adhesive tape which you envisage using is appropriate for your particular application. The Advisory Section of our Technical Service Department will be happy to assist. All information and recommendations are given by us in good faith, on the basis of practical experience, but without warranty.

# **Technical Data tesa 62932**

### Mean values / parameters of the specification

	immediately [N/cm]	after 14 days [N/cm]
Steel	13,0	= 17,0 <u>*</u>
Aluminium	13,0	= 17,0 <u>*</u>
ABS	14, 0	= 17,0 <u>*</u>
PC	9, 0	= 17,0 <u>*</u>
PS	10,5	= 17,0 <u>*</u>
РЕТ	12,5	= 17,0 <u>*</u>
PVC	14,5	= 17,0 <u>*</u>
PP	1,8	3,3
PE	1,7	3,0

### Peel adhesion on different surfaces:

\* foam splitting during measurement

#### **Temperature resistance**

Short Term	80 °C
Long Term	80 °C

### **Mechanical properties**

Tensile strength	≥ 12 N/15mm
Elongation	≥ 270 %

### **Results of laboratory evaluation**

Static shear re	sistance (1000 g	g / 13 mm x 2	20 mm)		
23°C			+		
40°C			+		
		ì		1	
Tack (Rolling Ball)			0		
[					
Softener resistance			0		
1					
Humidity resistance			++		
-					
Solvent resistance			+		
Ageing resistance (UV)			+		
Evaluation:	very good (++)	good ( + )	medium ( O )	low ( - )	

7100-05/06

tesa AG P.O. Box 57 02 62 D- 22771 Hamburg Telephone +49-40 49092618 Telefax +49-40 49094506 tesa self-adhesive tapes are used successfully in many sectors to solve a variety of problems. Our publications contain n umerous examples of such uses, intended to help towards a solution of your particular problems. Each tesa product has been developed for a particular range of applications. Nevertheless, experience has shown that even for one and the same obje ctive, the exact requirements may differ from case to case. We, therefore, recommend that you carry out your own tests in each case, to confirm that the tesa self-adhesive tape which you envisage using is appropriate for your particular application. The Advisory Section of our Technical Service Department will be happy to assist. All information and recommendations are given by us in good faith, on the basis of practical experience, but without warranty.