

# FWDFXX \*1) PA


e.g. FWDF15PA

\*1) xx No. of contacts 09, 15 or 25

xx	A mm	B mm	C mm
09	40	16.9	25
15	48.3	25.2	33.3
25	62	38.9	47.04

\*2) Dimension starts from front surface of shell (Part-No. 2)

max. torque are 40 Ncm  
 D-Sub connector with watertight frame,  
 Protection standard IP67, 100% checked  
 according to DIN EN 60529 (compl. mounted)



6	2	Threaded spacer	4-40/4-40 / Brass	tin plated
5	xx	Signal contact	P0 / Brass	AuroPur / 0.1-0.2µm Au / AWG 20
4	1	O-ring seal	Silicone / UL94V-0	red
3	1	Watertight frame	PBT	black
2	1	Shell	Brass	tin plated
1	1	Insulator	PBT (-25°C - +70°C)	red
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

Measurement without tolerance acc. to ISO 2768-sm		SCALE	TITLE
NAME / DATE	10.07.2013	2.1	Waterproof Connector System
DRAWN	Arke Meyer-Richter		
CHECKED	11.07.2013		

REV.	DATE	CH.-NO.	DWG.NO.	REPLACEMENT FOR:	PAGES
1			FWDFxxPA		1
					1

COMMENT:  
 ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,  
 IT MAY NOT BE REPRODUCED NOR MADE AVAILABLE TO A THIRD PARTY.  
 AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.