

Tip Jack Insulated Deluxe

SPECIFICATION

Contact: Brass body per QQ-B-626D with wrap around beryllium copper spring per QQ-C-533

Finish: Silver

Body: Nylon 66 per ASTM D4066

Std. Colors: Ten per FED-STD-595

Hardware: Nickel plated nut (unassembled)

Body Thread Stripping Torque: 4.0lb. in (4.5kg. cm)

Panel Thickness: Up to .437" (11.10mm)


RATINGS

Current: 10 amps

Breakdown Voltage: 5700 Vrms minimum

Contact Resistance: 0.010 ohm maximum

Contact-To-Panel C: 2pF nominal



For Standard Tip Plug: .080" (2mm) Diameter

FEATURES:

Machined contact with turret terminal

Hex socket head .188" (4.77mm) for ease in mounting

Closed entry blocks access of probes greater than .085" (2.16mm)

Nylon UL approved for self extinguishing

SILVER PLATING

Part Number	Color	Price	Part Number	Color	Price
105-0601001	White	\$ 94.80 C	105-0607001	Yellow	\$94.80 C
105-0602001	Red	94.80 C	105-0608001	Brown	94.80 C
105-0603001	Black	94.80 C	105-0610001	Blue	94.80 C
105-0604001	Green	94.80 C	105-0612001	Violet	94.80 C
105-0606001	Orange	94.80 C	105-0613001	Gray	94.80 C

Tip Jack Insulated Standard

SPECIFICATION

Contact: Phosphor bronze per QQ-B-750

Finish: Bright tin

Body: Nylon 66 per ASTM D4066

Std. Colors: Ten per FED-STD-595

Hardware: Nickel plated nut (unassembled)

Body Thread Stripping Torque: 4.0lb. in (4.5kg. cm)


Panel Thickness: Up to .437" (11.10mm)

RATINGS

Current: 10 amps

Breakdown Voltage: 5700 Vrms minimum

Contact Resistance: 0.010 ohm maximum



For Standard Tip Plug: .080" (2mm) Diameter

FEATURES:

Formed Contact

Hex socket head .188" (4.77mm) for ease in mounting

Nylon UL approved for self extinguishing

BRIGHT TIN PLATING

Part Number	Color	Price	Part Number	Color	Price
105-0801-001	White	\$ 51.10 C	105-0807-001	Yellow	\$ 51.10 C
105-0802-001	Red	51.10 C	105-0808-001	Brown	51.10 C
105-0803-001	Black	51.10 C	105-0810-001	Blue	51.10 C
105-0804-001	Green	51.10 C	105-0812-001	Violet	51.10 C
105-0806-001	Orange	51.10 C	105-0813-001	Gray	51.10 C

Tip Jacks Insulated .125"

SPECIFICATION

Contact: Phosphor bronze per QQ-B-750

Finish: Bright tin

Body: Nylon 66 per ASTM D4066

Std. Colors: Seven per FED-STD-595

Hardware: Nickel plated nut (unassembled)

Body Thread Stripping Torque: 4.0lb. in (4.5kg. cm)

Panel Thickness: Up to .437" (11.10mm)


RATINGS

Current: 10 amps

Breakdown Voltage: 5700 Vrms minimum

Contact Resistance: 0.010 ohm maximum

Contact-To-Panel C: 2 pF nominal



For Standard Tip Plug: .125" (3.2mm) Diameter

FEATURES:

Formed Contact with slotted terminal

Hex socket head .188" (4.77mm) for ease in mounting

Nylon UL approved for self extinguishing

BRIGHT TIN PLATING

Part Number	Color	Price	Part Number	Color	Price
105-1001-001	White	\$1.02 E	105-1007-001	Yellow	\$ 1.02 E
105-1002-001	Red	1.02 E	105-1008-001	Brown	1.02 E
105-1003-001	Black	1.02 E	105-1010-001	Blue	1.02 E
105-1004-001	Green	1.02 E			

Tip Plugs Insulated Solderless Type

SPECIFICATION

Contact: Brass per QQ-B-626D

Finish: Nickel

Insulated Handle: Nylon 66 per ASTM D4066


Std. Colors: Ten per FED-STD-595

RATINGS

Current: 10 amps

Breakdown Voltage: 3500 Vrms minimum

Contact Resistance: 0.010 ohm maximum



For Standard Tip Jack: .080" (2mm) Diameter

FEATURES:

Recessed head to reduce shock hazard

Accepts wire sizes up to 16 gauge

Nylon UL approved for self extinguishing

NICKEL PLATING

Part Number	Color	Price	Part Number	Color	Price
105-0301-001	White	\$ 69.40 C	105-0307-001	Yellow	\$ 69.40 C
105-0302-001	Red	69.40 C	105-0308-001	Brown	69.40 C
105-0303-001	Black	69.40 C	105-0310-001	Blue	69.40 C
105-0304-001	Green	69.40 C	105-0312-001	Violet	69.40 C
105-0306-001	Orange	69.40 C	105-0313-001	Gray	69.40 C

Tip Plug Insulated Stacking: Single Type

SPECIFICATION

Contact: Brass body per QQ-B-626D with wrap around beryllium copper spring per QQ-C-533
Silver Plated

Finish: Nickel

Insulated Handle: Nylon 66 per ASTM D4066


Std. Colors: Six per FED-STD-595

RATINGS

Current: 10 amps

Breakdown Voltage: 3500 Vrms minimum

Contact Resistance: 0.010 ohm maximum



For Standard Tip Jack: .080" (2mm) Diameter

FEATURES:

Solderless type connection

Closed entry blocks access of probes greater than .085" (2.16mm)

Accepts wire up to 16 gauge

Nylon UL approved for self extinguishing

NICKEL PLATING

Part Number	Color	Price	Part Number	Color	Price
105-1201-001	White	\$ 2.44 E	105-1204-001	Green	\$ 2.44 E
105-1202-001	Red	2.44 E	105-1207-001	Yellow	2.44 E
105-1203-001	Black	2.44 E	105-1210-001	Blue	2.44 E