

**Path:** [Home](#) > [Enclosure Index](#) > [Watertight - Non Metallic Enclosures](#) > **ABS Plastic**



## Key Information:

- **Application**

ABS plastic enclosures are designed for use as instrument enclosures, electrical junction boxes or terminal wiring enclosures where metallic enclosures are not suitable.

Provide outstanding protection against dust, oil and pressurized water.

Impervious to atmospheric and marine corrosion.

- **Standards**

NEMA Type 4, 4X, 12 and 13

IEC 529, IP66

UL94 HB Flammability Rating

- **Construction**

Molded in ABS plastic.

Unique reversible bottom and cover section.

Separate mounting channels provide access to rear mounting position without opening the enclosure.

Recessed polyurethane gasket with tongue and groove construction.

Interlocking flange on cover and bottom sections.

Captive stainless steel cover screws are provided.

Cover screws fasten into pre-threaded holes.

Unique snap on screw covers hide the cover fastening screws for a highly finished appearance.

- **Finish**

Light grey RAL 7035

- **Front plates, Internal Hinges, Mounting Feet and P.C. Board Supports available** \_\_\_\_\_

Shallow Depth - ABS Plastic

Part No.	Units	Width	Length	Height
		A	B	C
R200-122-000	mm	120	200	60
	inches	4.8	8	2.4