

## SAFETY DATA SHEET WASH AND WAX

### SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

#### 1.1. Product identifier

Product name WASH AND WAX  
Product No. PWW005, AFS505, PRC500, AFE000

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.3. Details of the supplier of the safety data sheet

Manufacturer TETROSYL LIMITED  
BEVIS GREEN WORKS  
WALMERSLEY  
BURY  
BL9 6RE  
0161 764 5981  
0161 797 5899  
info@tetrosyl.com

#### 1.4. Emergency telephone number

0161 764 5981

### SECTION 2: HAZARDS IDENTIFICATION

#### 2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards	Not classified.
Human health	Eye Dam. 1 - H318
Environment	Not classified.

Classification (1999/45/EEC) Xi;R36.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

#### 2.2. Label elements

Detergent Labelling:

5 - < 15%	non-ionic surfactants
< 5%	perfumes
Contains	Benzisothiazolinone,LINALOOL,Methylisothiazolinone

Label In Accordance With (EC) No. 1272/2008



Signal Word Danger

Hazard Statements

H318 Causes serious eye damage.

**WASH AND WAX**

## Precautionary Statements

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P280	Wear eye and face protection.
P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310	Immediately call a POISON CENTER or doctor/physician.

**2.3. Other hazards****SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS****3.2. Mixtures**

ALCOHOLS, C12 - 14, ETHOXYLATED	1.0 - <3.0%
CAS-No.: 68439-50-9	EC No.:
Classification (EC 1272/2008) Acute Tox. 4 - H302 Eye Dam. 1 - H318	Classification (67/548/EEC) Xn;R22. Xi;R41.
AMIDES, COCO, N-[3-(DIMETHYLAMINO)PROPYL], N-OXIDE	0.1 - <0.3%
CAS-No.: 68155-09-9	EC No.: 268-938-5
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Dam. 1 - H318 Aquatic Chronic 2 - H411	Classification (67/548/EEC) Xi;R38,R41. N;R51/53.
DIETHYLENE GLYCOL	0.0001 - <0.1%
CAS-No.: 111-46-6	EC No.: 203-872-2
Classification (EC 1272/2008) Acute Tox. 4 - H302	Classification (67/548/EEC) Xn;R22
FATTY ACIDS, C18 UNSATD., REACTION PRODUCTS WITH TRIETHANOLAMINE, DI-ME SULFATE-QUATERNIZED	1.0 - <3.0%
CAS-No.: 1335202-95-3	EC No.: 931-216-1
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Irrit. 2 - H319	Classification (67/548/EEC) Xi;R36/38.

**WASH AND WAX**

FATTY ALCOHOL ETHOXYLATE		5.0 - <10.0%
CAS-No.: 68439-45-2	EC No.:	
Classification (EC 1272/2008)	Classification (67/548/EEC)	
Acute Tox. 4 - H302	Xn;R22.	
Eye Dam. 1 - H318	Xi;R41.	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

**SECTION 4: FIRST AID MEASURES****4.1. Description of first aid measures**

## General information

Get medical attention if any discomfort continues. General first aid, rest, warmth and fresh air. NOTE! Effects may be delayed. Keep affected person under observation. Remove affected person from source of contamination.

## Inhalation

In case of inhalation of spray mist: Move person into fresh air and keep at rest.

## Ingestion

Provide rest, warmth and fresh air. Immediately rinse mouth and drink plenty of water. If person becomes uncomfortable or if ingested in large amounts (100-150 ml for an adult person): Take to hospital along with these instructions.

## Skin contact

Remove contaminated clothing immediately and wash skin with soap and water. Rinse with water. Get medical attention if any discomfort continues.

## Eye contact

Important! Immediately rinse with water for at least 15 minutes. Make sure to remove any contact lenses from the eyes before rinsing. Get medical attention promptly if symptoms occur after washing.

**4.2. Most important symptoms and effects, both acute and delayed**

## General information

The severity of the symptoms described will vary dependant of the concentration and the length of exposure. NOTE! Effects may be delayed. Keep affected person under observation.

## Inhalation

No specific symptoms noted.

## Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting.

## Skin contact

Skin irritation. Prolonged or repeated contact with skin may cause redness, itching, irritation and eczema/chapping. Blistering may occur.

## Eye contact

Irritating and may cause redness and pain. May cause blurred vision and serious eye damage.

**4.3. Indication of any immediate medical attention and special treatment needed**

No recommendation given, but first aid may still be required in case of accidental exposure, inhalation or ingestion of this chemical. If in doubt, GET MEDICAL ATTENTION PROMPTLY!

**SECTION 5: FIREFIGHTING MEASURES****5.1. Extinguishing media**

**WASH AND WAX****Extinguishing media**

Use: Foam, carbon dioxide or dry powder. Water. Use fire-extinguishing media appropriate for surrounding materials.

**5.2. Special hazards arising from the substance or mixture****Hazardous combustion products**

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

**Unusual Fire & Explosion Hazards**

No unusual fire or explosion hazards noted.

**Specific hazards**

Fire creates: Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

**5.3. Advice for firefighters****Special Fire Fighting Procedures**

No specific fire fighting procedure given.

**Protective equipment for fire-fighters**

Leave danger zone immediately.

**SECTION 6: ACCIDENTAL RELEASE MEASURES****6.1. Personal precautions, protective equipment and emergency procedures**

For personal protection, see section 8. In case of spills, beware of slippery floors and surfaces. Avoid contact with skin and eyes.

**6.2. Environmental precautions**

Avoid discharge into water courses or onto the ground.

**6.3. Methods and material for containment and cleaning up**

No specific clean-up procedure noted.

**6.4. Reference to other sections**

For personal protection, see section 8. For waste disposal, see section 13.

**SECTION 7: HANDLING AND STORAGE****7.1. Precautions for safe handling**

Good personal hygiene is necessary. Wash hands and contaminated areas with water and soap before leaving the work site. Avoid eating, drinking and smoking when using the product. Avoid contact with skin and eyes. Do not handle broken packages without protective equipment.

**7.2. Conditions for safe storage, including any incompatibilities**

Keep upright. Store in tightly closed original container.

**7.3. Specific end use(s)**

The identified uses for this product are detailed in Section 1.2.

**SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION****8.1. Control parameters**

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
DIETHYLENE GLYCOL	WEL	23 ppm	101 mg/m <sup>3</sup>			

WEL = Workplace Exposure Limit.

**WASH AND WAX****8.2. Exposure controls**

## Protective equipment



## Process conditions

Provide eyewash, quick drench.

## Engineering measures

Weighing/dispensing only in well ventilated area.

## Respiratory equipment

No specific recommendation made, but respiratory protection may still be required under exceptional circumstances when excessive air contamination exists.

## Hand protection

Protective gloves should be used if there is a risk of direct contact or splash. Nitrile gloves are recommended, but be aware that the liquid may penetrate the gloves. Frequent change is advisable.

## Eye protection

Wear approved chemical safety goggles where eye exposure is reasonably probable.

## Other Protection

Wear appropriate clothing to prevent any possibility of skin contact. Provide eyewash station.

## Hygiene measures

Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. Wash hands after contact. Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes wet or contaminated. Wash contaminated clothing before reuse.

**SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES****9.1. Information on basic physical and chemical properties**

Appearance	Clear liquid.
Colour	Yellowish
Odour	Characteristic.
Solubility	Soluble in water.
Initial boiling point and boiling range (°C)	>100°C
Melting point (°C)	Not determined.
Relative density	Scientifically unjustified. 1.01
Vapour density (air=1)	Not determined.
Vapour pressure	Scientifically unjustified.
Evaporation rate	Not determined.
pH-Value, Conc. Solution	Scientifically unjustified. 5.0 - 6.0
Viscosity	200 cP 20°C
Decomposition temperature (°C)	Not determined.
	Scientifically unjustified.

**WASH AND WAX**

Odour Threshold, Lower  
Not determined.

Scientifically unjustified.

Odour Threshold, Upper  
Not determined.

Scientifically unjustified.

Flash point (°C)

>100°C

Auto Ignition Temperature (°C)

Not determined.

Scientifically unjustified.

Flammability Limit - Lower(%)

Not determined.

Scientifically unjustified.

Flammability Limit - Upper(%)

Not determined.

Scientifically unjustified.

Partition Coefficient

(N-Octanol/Water)

Not determined.

Scientifically unjustified.

Oxidising properties

Not determined.

**9.2. Other information**

None.

**SECTION 10: STABILITY AND REACTIVITY****10.1. Reactivity**

No specific reactivity hazards associated with this product.

**10.2. Chemical stability**

No particular stability concerns.

**10.3. Possibility of hazardous reactions**

Not determined.

**10.4. Conditions to avoid**

Avoid excessive heat for prolonged periods of time.

**10.5. Incompatible materials**

Materials To Avoid

No specific, or groups of materials are likely to react to produce a hazardous situation.

**10.6. Hazardous decomposition products**

None under normal conditions.

**SECTION 11: TOXICOLOGICAL INFORMATION****11.1. Information on toxicological effects**

Toxic Dose 1 - LD 50

500-2000 (ALCOHOLS, C12-14, ETHOXYLATED) mg/kg (oral rat)

**WASH AND WAX**

Eye contact  
Irritating to eyes.

**Health Warnings**

This chemical can be hazardous when inhaled and/or touched. This chemical may cause skin/eye irritation and burns (corrosive). May cause severe internal injury. Vapour from this chemical can be hazardous when inhaled.

**Route of entry**

Inhalation. Ingestion. Skin and/or eye contact. Skin absorption.

---

**SECTION 12: ECOLOGICAL INFORMATION**

---

**Ecotoxicity**

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

**12.1. Toxicity**

LC 50, 96 Hrs, Fish mg/l 0.4-10 (ALCOHOLS, C12-14, ETHOXYLATED)

Acute Toxicity - Aquatic Invertebrates

Not determined.

Acute Toxicity - Aquatic Plants

Not determined.

**12.2. Persistence and degradability**

Degradability

No data available.

**12.3. Bioaccumulative potential**

Bioaccumulative potential

No data available on bioaccumulation.

Partition coefficient

Not determined.

Scientifically unjustified.

**12.4. Mobility in soil**

Mobility:

The product is soluble in water.

Adsorption/Desorption Coefficient

Not available.

**12.5. Results of PBT and vPvB assessment**

Not Classified as PBT/vPvB by current EU criteria.

**12.6. Other adverse effects**

Not applicable.

---

**SECTION 13: DISPOSAL CONSIDERATIONS**

---

**General information**

Waste to be treated as controlled waste. Disposal to licensed waste disposal site in accordance with local Waste Disposal Authority.

**13.1. Waste treatment methods**

Dispose of waste and residues in accordance with local authority requirements. Confirm disposal procedures with environmental engineer and local regulations.

---

**SECTION 14: TRANSPORT INFORMATION**

---

**WASH AND WAX**

General The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).

**14.1. UN number****14.2. UN proper shipping name****14.3. Transport hazard class(es)**

Transport Labels

No transport warning sign required.

**14.4. Packing group****14.5. Environmental hazards**

Environmentally Hazardous Substance/Marine Pollutant  
No.

**14.6. Special precautions for user****14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

Not applicable.

**SECTION 15: REGULATORY INFORMATION****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

EU Legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

**15.2. Chemical Safety Assessment**

No chemical safety assessment has been carried out.

**SECTION 16: OTHER INFORMATION**

Revision Comments

NOTE: Lines within the margin indicate significant changes from the previous revision.

Revision Date 11/04/2014  
Revision 6  
Supersedes date 26/03/2014 V5  
Safety Data Sheet Status Approved.

Risk Phrases In Full

R22 Harmful if swallowed.  
R36/38 Irritating to eyes and skin.  
R36 Irritating to eyes.  
R38 Irritating to skin.  
R41 Risk of serious damage to eyes.  
R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.



## WASH AND WAX

### Hazard Statements In Full

H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H315	Causes skin irritation.
H302	Harmful if swallowed.
H411	Toxic to aquatic life with long lasting effects.