

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-12-2024

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Solid Header, Right Angle, with Friction Lock, 2 Circuits, 0.51µm Gold (Au) Plating

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

7478

Signal, Wire-to-Board

KK® Interconnect System - Molex

KK® 254

800753592179

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Compliant

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

2

2

Natural (White)

50

94V-0

No

Yes

Brass

Gold

Gold

Nylon

0.252/g

1

Right Angle

3.58mm

No

None

1.60mm

Bag

2.54mm

2.54mm

0.508µm

0.508µm

Yes

Yes

Partial

Yes

See Product Specification

Through Hole

Electrical

Current - Maximum per Contact

4A



image - Reference onlySeries

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7478Series

Mates With

2695 , 6471 , 7880 , 4455 , 7720

Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235
Material Info	
Old Part Number	A-7478-02A241
Reference - Drawing Numbers	
Product Specification	PS-10-07, RPS-6373-001
Sales Drawing	SDA-7478

This document was generated on 07/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION