


# BNC Plug Elbow, Clamp, 75R



## Specifications:

Connector Type	: BNC Coaxial
Body Style	: Right Angle Plug
Outer Coaxial Termination	: Clamp
Inner Coaxial Termination	: Solder
Impedance	: 75Ω
Coaxial Cable Types	: RG-59
Frequency Max	: 1GHz
Connector Mounting	: Cable
Cable Diameter Max	: 6.15mm
Contact Resistance	: 1.5mΩ
DC Current Max	: 1A
Operating Frequency Max	: 11GHz
Operating Temperature	: -65°C to +165°C
Proof Voltage	: 2kV
Termination Method	: Clamp
VSWR	: 1.35
Working Voltage	: 500V
Bodies	: Brass per JIS-C3604
Centre Contact	: Brass per JIS-C3604
Insulation	: PTFE per ASTM D1457 and ASTM D1710

Part to be clean and free of burrs



Dimensions : Millimetres (Inches)

Stripping Dimension



# BNC Plug Elbow, Clamp, 75R



Number	Description	Material	Finish	
1	Shell	Zinc	Nickel 100µ" Min.	
2	Insulation	PTFE	None	
3	Gasket	Rubber		
4	Washer	Brass	Nickel 100µ" Min.	
5	Spring Washer	SK-5		
6	Washer	Brass		
7	Body I			
8	Centre Contact			Gold
9	Body II			
10	Nut I			
11	Chassis	Nickel 100µ" Min.		
12	Braid Clamp	Rubber	None	
13	Gasket			
14	Washer			
15	Nut II	Brass	Nickel 100µ" Min.	

## Part Number Table

Description	Part Number
Plug, BNC, Elbow, Clamp, 75R, RG59	13-06-4 TGN RG59

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com  
www.farnell.com  
www.newark.com

