


CUSTOMER	MCM	FILE NO.	25-257
----------	-----	----------	--------


THIS DRAWING AND SPECIFICATIONS, HEREIN ARE THE CONFIDENTIAL PROPERTY OF SAMAR AND SHALL NOT BE REPRODUCED OR COPIED OR DISCLOSED IN WHOLE OR IN PART WITHOUT WRITTEN PERMISSION.

REV.	DESCRIPTION	DRAWN / DATE	APPROVED / DATE
0	INITIAL RELEASE	FROS 07/14/2014	FROS 07/14/2014



NOTES:

- POWER DISSIPATION: 80mW
- FORWARD CURRENT: 30mA
- PEAK FORWARD CURRENT: 150mA
- REVERSE VOLTAGE: 5V
- OPERATING TEMPERATURE: -40°C~80°C
- STORAGE TEMPERATURE: -40°C~85°C
- SOLDERING TEMPERATURE: 260°C MAX FOR 5 SECONDS
- HAND SOLDERING TEMPERATURE: 350°C MAX FOR 3 SECONDS



RoHS

DIMENSIONS ARE IN mm	TOLERANCES ARE FRACTIONS DECIMALS ANGLES	MATERIAL		P/N	25-257	DRAWN	FROS	DATE	07/14/2014
MOLD NO.	± 0.25	FINISH		PROJECT NO.					
25-257		COLOR		SCALE	5/1	SIZE	A4	SHEET	1 OF 1

3MM GREEN LAMP