



Description

- Temperature compensated voltage controlled crystal oscillator (TCVCXO)
- Model IQXT-200-4-B
- Model Issue number 1

Frequency Parameters

- Frequency 10.0MHz
- Frequency Tolerance @ 25°C ±0.50ppm
- Frequency Stability ±0.28ppm
- Operating Temperature Range -20.00 to 70.00°C
- Ageing ±0.02ppm max per day, ±1ppm max per year
- Supply Voltage Variation (measurement referenced to frequency observed with TA=25°C, Vs varied from 3.13V to 3.47V, VC=1.65V and load=10kΩ//10pF): ±0.1ppm max
- Load Variation (5% load change measurement referenced to frequency observed with TA=25°C, Vs=3.3V, VC=1.65V and load=10kΩ//10pF): ±0.1ppm max
- Frequency Tolerance (measurement referenced to frequency observed with TA=25°C, Vs=3.3V, VC=1.65V and within 30 days after ex-works): ±0.5ppm
- Short Term Stability (@ 25°C after 10mins power on): 5E-10/s typ @ 10MHz
- Frequency Stability: TA varied from -20°C to 70°C, measurement referenced to frequency observed with TA=25°C, Vs=3.3V, VC=1.65V, load=10kΩ//10pF and temperature variable speed less than 2°C per minute.
- Ageing: TA=25°C, Vs= 3.3V, VC=1.65V and after 1hr of operation.

Electrical Parameters

- Supply Voltage 3.3V
- Supply Voltage Tolerance ±5%
- Current Draw 10.00mA max
- Current: TA=25°C, Vs=3.3V, VC=1.65V and load=10kΩ//10pF

Frequency Adjustment

- Pulling ±10ppm to ±15ppm
- Control Voltage Details 1.65V ±1.65V
- Linearity: ±10% max
- Input Impedance: 100kΩ min
- Slope: Positive

Output Details


- Output Compatibility Clipped Sine
- Output Load 10kΩ//10pF
- Output Level: 0.8V pk-pk min

Noise Parameters


- Phase Noise (@ 10MHz typ):
 - 90dBc/Hz @ 10Hz
 - 115dBc/Hz @ 100Hz
 - 135dBc/Hz @ 1kHz
 - 145dBc/Hz @ 10kHz
 - 148dBc/Hz @ 100kHz
 - 150dBc/Hz @ 1MHz



Outline (mm)



- Pad Connections
- Voltage Control
 - GND
 - Output
 - +Vs
- D1, D2, D3, D4. N/C



Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: +49 (0)7264 9145-62

France: +33 (0)5 34 50 91 18
USA: +1 408.273.4530

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com



Environmental Parameters

- Shock: IEC 60068-2-27, Test Ea: 100G acceleration for 6ms, sinewave, in 3 mutually perpendicular planes
- Vibration: IEC 60068-2-6, Test Fc: 10Hz-2000Hz, 0.75mm amplitude, 10G acceleration, 30mins per cycle, in 3 mutually perpendicular planes, test duration 2hrs
- Storage Temperature Range: -55 to 105°C
- ESD Level:
HBM, Class 2: 2000V to 4000V, JEDEC JS-001-2010
Machine Model, Class B: 200V to 400V, JEDEC JS-001-2010

Manufacturing Details

- Moisture Sensitivity Level: 2
- Maximum Reflow Temperature: 260°C (30secs max)

Compliance

- RoHS Status Compliant
- REACh Status Compliant

Packaging

- Pack Type: Bulk Loose in bulk pack
Pack Size 1
- Alternative packing option available

This document is correct at the time of printing; please contact your local office for the latest version.

Sales Office Contact Details:

UK: +44 (0)1460 270200

France: +33 (0)5 34 50 91 18

Email: info@iqdfrequencyproducts.com

Germany: +49 (0)7264 9145-62

USA: +1 408.273.4530

Web: www.iqdfrequencyproducts.com