





Designed to comply with physical, electrical and environmental requirements of full size USB Standard Compliance (USB3.0).



Specifications 规格:

Materials 材料:

Plastic Housing 塑胶外壳: LCP, UL94V-0 Blue

Contact Terminal 接触端子: Copper Alloy 铜合金

Metallic Shell 金属外壳: Brass (Back Lid - SPCC)

Finish 表面处理:

Underplating 底层电镀: Nickel

Plating 电镀:

Contact Area 接触面积: 30μ" Gold

Solder Tails 焊接末端: 100μ" min. Tin

Metallic Shell 金属外壳: Nickel

Electrical 电气规格:

Voltage Rating 电压额定值: 100 V AC

Current Rating 电流额定值:

0.25A (Signal Pins 信号引脚 2,3,5,6,7,8,9)

1.8A (Power Pins 电源引脚 1,4)

Operating Temperature 工作温度: -55°C to +85°C

Contact Resistance 接触电阻值: 30 mΩ max.

Insulating Resistance 绝缘电阻值: 1000 MΩ min.

Dielectric Withstand Voltage 耐电压: 100V AC/minute

Mechanical 机械性规格:

Mating Force 插入力: 35N max.

Unmating Force 拔出力: 10N min. initial, 8N min. after test

Durability 耐久性: 5000

Ordering Grid

USB1080

30

B REQUEST SAMPLES AND QUOTATION

Contact Plating
30 = 30μ" Gold

Packing Options
B = Tray
(120 per tray)

By	AJO
DETAIL	USB1080 X PCN
REV	X
DATE	15/05/14





Tolerances (Except as noted)	
Dimensions in mm	
X.X ± 0.3	X.X° ± 2°
X.XX ± 0.25	X.XX° ± 1°
X.XXX ± 0.1	X.XXX° ± 0.5°
Third Angle Projection	

Part Number:-		Date:-	
USB1080		23 SEP 11	
Description:-			
USB 3.0 Receptacle, Type B, Through Hole, Horizontal, 9 Pin, With Kinked Shell Stakes			
© THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT			



GCT
www.gct.co

Scale	Revision	Material	Drawn by	E & OE	Sheet No.
NTS	X	See Note	ASE		1/2

Products P/N	PCS/Tray	Trays/Carton	PCS/Carton
USB1080-30-B	120	17	2040




②




③

17 trays
per box
每盒17盘



④

Tape
膠帶



Packing Rules封裝規則:

- 1.USB's placed into the tray base. 將USB连接器放入吸塑盘內
- 2.Tray cover and base taped together to keep USB's in place. USB连接器放好后，加上吸塑盖，并用胶带缠绕好
- 3.17 trays put into carton. 17吸塑盘一叠，放入纸箱
- 4.Boxed taped and label stuck on the outer carton. 用胶带封住纸箱；并贴上标签。

By	AJO
DETAIL	USB1080 X PCN
REV	X
DATE	15/05/14



Tolerances (Except as noted)	
Dimensions in mm	
X.X ± 0.3	X.X° ± 2°
X.XX ± 0.25	X.XX° ± 1°
X.XXX ± 0.1	X.XXX° ± 0.5°
Third Angle Projection	

Part Number:-	Date:-
USB1080	23 SEP 11
Description:-	
USB 3.0 Receptacle, Type B, Through Hole, Horizontal, 9 Pin, With Kinked Shell Stakes	
© THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT	

Scale NTS	Revision X	Material See Note	Drawn by ASE	Sheet No. 2/2
--------------	---------------	----------------------	-----------------	------------------

GCT
www.gct.co