

Strip Block for Snap-in Mounting with up to 7 IEC Appliance Outlets F




Snap-In Version



Snap-In Version



Snap-In Version



Description

- Panel Mount
- Snap-in version from front side
- 1 Function
- Module of 2 up to 7 outlets,
- Pin temperature 70 °C, Protection class I
- Solder terminals

Approvals

- VDE Certificate Number: 40030907
- UL File Number: E103791

Characteristics

- Suitable for use in equipment according to IEC/UL 60950

Other versions on request

- Other panel thickness

Weblinks


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [CAD-Drawings](#), [Accessories](#), [Detailed request for product](#)

Technical Data

Ratings IEC	10A / 250VAC; 50Hz
Ratings UL/CSA	15A / 250VAC; 60Hz
Dielectric Strength	> 2 kVAC between L-N > 2 kVAC between L/N-PE (1 min/50Hz)
Allowable Operation Temp.	-25 °C to 70 °C
Degree of Protection	from front side IP 30 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140
Terminal	Solder terminals
Panel Thickness s	Snap-in 1.5 mm tolerance +0.0/-0.1
Material: Housing	Thermoplastic, black, UL 94V-0

Appliance Outlet	F acc. to IEC 60320, UL 498 CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10A, Protection Class I
MTBF	> 200'000h acc. to MIL-HB-217 F

Dimensions



All Variants

Panel Thickness [mm]	Connector	Length L1 [mm]	Length L2 [mm]	Packaging unit	Order Number	
1.5	2	51.2mm	48.3mm	120	0909.0001	■
1.5	3	75.2mm	72.3mm	80	0909.0011	
1.5	4	99.2mm	96.3mm	60	0909.0021	■
1.5	5	123.2mm	120.3mm	40	0909.0031	■
1.5	6	147.2mm	144.4mm	40	0909.0041	■
1.5	7	171.2mm	168.4mm	32	0909.0051	■

■ Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Accessories

Description



[Cord retaining kits](#)
Cord retaining strain relief

Mating Inlets/Plugs

Category / Description

[Plug Overview complete](#)

IEC Plug E, Cord Connector (Rewireable), Straight, max. cable Diameter 8.5 mm	4732
IEC Plug E, Cord Connector (Rewireable), Angled, max. Cable Diameter 8.5 mm	4733
IEC Plug E, Cord Connector (Rewireable), Straight, max. Cable Diameter 10 mm	4735
IEC Plug E, Cord Connector (Rewireable), Angled, max. Cable Diameter 10 mm	4736
IEC Plug E, Cord Connector (Rewireable), Straight	9009
Plug further types to 0909	...