



ALL DIMENSIONS IN MM / ANGLES IN DECIMAL DEGREES



SPECIFICATIONS

- VOLTAGE 500V_{ac}
- FREQUENCY 50/60Hz
- CURRENT 36A @ 40°C
- TEMPERATURE -25 TO 100°C
- LEAKAGE CURRENT 42mA @ 500V 50Hz
- HUMIDITY 90% RH (NON-CONDENSING)
- VIBRATION 10-200Hz 1.8G
- SURGE 4000Vpk 1.2/50 μ s
- ELECTRIC STRENGTH 2250V_{ac}/min.
- POWER DISSIPATION 16W
- MASS 2.7kg
- TERMINALS 10sqmm TERMINAL BLOCK
- EARTH TERMINALS M6 STUD
- FLANGE MOUNTING 4x M6



ROXBURGH ELECTRONICS LTD

TITLE 3 PHASE 36A 500V INDUSTRIAL FILTER

Drg No
KMF336-GS

ISSUE
1

GENERAL SPECIFICATION
FOR KMF336

CUSTOMER
REFERENCE