



Main

Range of product	Harmony XVP Universal
Product or component type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit with black clamping ring
Signalling type	Flashing
Mounting diameter	50 mm
Component name	XVPC
Material	Polycarbonate and polyamide
Light source	Green integral flash discharge tube
Bulb type	Flash discharge tube
[Us] rated supply voltage	120 V AC
Flash energy	0.6 J

Complementary

Assembly style	Customer assembly, up to 5 units
Connections - terminals	Screw clamp terminals: $\leq 1 \times 1.5 \text{ mm}^2$ with cable end
Marking	CE
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
Nominal voltage limit	0.85...1.1 U_n conforming to IEC 60947-5-1
Current consumption	$\leq 20 \text{ mA AC}$
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
Flashing frequency	0.6...2 Hz
Service life in hours	> 1000 h (-25...50 °C)
CAD overall width	56 mm
CAD overall height	65 mm
CAD overall depth	56 mm
Product weight	0.115 kg

Environment


Product certifications	CULus
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Class of protection against electric shock	Class II on base unit conforming to IEC 61140 Class I on support tube conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Indicator Bank without Audible Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



Number of illuminated units	b in mm	b in in.
1	108	4.25
2	170	6.69
3	232	9.13
4	294	11.57
5	356	14.02