



Main

Range of product	Harmony XVS
Product or component type	Multisound siren
Device short name	XVS

Complementary

Colour	White
Material	PC/ABS (body)
Product weight	1.2 kg
Marking	CE
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	100 mA at 120 V
Electrical connection	Cable: 6.5...8.5 mm, 0.52 mm ² / AWG 20 (power circuit) Cable : 6.5...8.5 mm, 0.33 mm ² / AWG 22 (signalling circuit)
Width	140 mm
Height	114 mm
Depth	223 mm

Environment

Signalling type	43 tones siren
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Class of protection against electric shock	Class II conforming to EN/IEC 61140
IP degree of protection	IP53 conforming to EN/IEC 60529
[Us] rated supply voltage	120 V AC
Noise level	0...105 dB (continuous or intermittent tone) at 1 m

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0808 - Schneider Electric declaration of conformity

Siren

Dimensions

