

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-01-2075

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Housing, Friction Ramp, 7 Circuits



Series

image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07 (PDF)

Product Specification PS-99020-0088 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19880

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

Crimp Housings

6471

Signal, Wire-to-Board

KK® Interconnect System - Molex

KK® 254

800753741089

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

7

Natural (White)

94V-0

Female

No

Yes

Nylon

0.721/g

1

Bag

No

2.54mm

2.54mm

Yes

No

See Product Specification

Solder Process Data

Lead-free Process Capability

Wave Capable (TH only)

Material Info

Old Part Number

6471-07(I)

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-10-07, PS-99020-0088

SD-6471-N*~**, SDE-6471-N*~*

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

6471Series

Mates With

KK®254 PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[2759](#) , [4809](#) KK® Crimp terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION