9176-500





The 917X series of surface mount Insulation Displacement Connectors (IDC) were developed to meet the harsh automotive and industrial market applications for connecting individual wires directly to a PCB ranging from 14 AWG to 28 AWG. This industry proven contact system has been tested to automotive levels of shock, vibration, and temperature cycling to prove their reliability and robustness. This new single contact was developed as a standalone component to enhance the application uses with the IDC technology. The simplicity of inserting a wire into an SMT contact with a small tool or optional retention / termination cap allows a wide range of devices to be connected to the PCB without soldering. In SSL applications specifically, these contacts are used to bring power and signal onto the PCB or are used to daisy chain multiple boards together in a long string. While the IDC contact provides a gas-tight connection to conductor of the wire, the optional cap provides a positive strain relief even in the harshest conditions. In case of repair, the wires can be removed and replace up to three times.

The single 9176 series contact and cap accepts 18 AWG to 24 AWG wires with an insulation diameter ranging from 1.1mm to 2.1mm. These dual beam contacts support a 10 amp current rating with a large SMT solder base to provide maximum stability on the PCB. The optional locking strain relief cap acts as the termination tool for severe vibration applications.

APPLICATIONS

- Connecting discrete wire components directly to the PCB
- Bringing power and signals onto a PCB
- Daisy chaining PCB's together to create a continuous string of boards
- Application notes: refer to 201-01-124

FEATURES AND BENEFITS

- IDC contact is supplied in T&R pockets for standard SMT placement
- IDC contact provides a gas-tight connection to the PCB for long term reliability
- Optional termination cap provides additional strain relief for severe environments
- · Tested to automotive levels on shock, vibration and temperature cycling for reliability
- Reduced total applied cost versus solder or crimp processes
- Individual contacts can be located anywhere on the PCB based on specific application

ELECTRICAL

- Current Rating: 10 Amps/Contact
- Voltage Rating: Dependent on component proximity


ENVIRONMENTAL

• Operating Temperature: -40°C to +125°C

MECHANICAL

- Insulator Material: Nylon 46: UL94V0
- Contact Material: Phosphor Bronze
- Plating: Tin over Nickel
- Durability: 3 Cycles


HOW TO ORDER - CONTACT OPTIONS



Wile dauge Oize				
Code	Accepted Wire Gauge			
501 18 Gauge Stranded				
511	20 Gauge Solid or Stranded			
522	22 Gauge Solid or Stranded			
532	24 Gauge Solid or Stranded			



HOW TO ORDER - CAP OPTIONS



CONNECTOR/TOOLING PART NUMBER MATRIX

SERIES 9176-500 IDC			00 IDC	HAND INSERTION TOOLING*		ACCESSORY CAPS		
AWG	Wire Insulation	Positions	Part Number	Plastic (medium volume)	Metal (high volume)	Cap Application Tool	White	Black
18	Ø 1.6 - 2.1	1p	709176001501006	069176702001000	069176701901000	069176701801000	609176001521100	609176001521000
20	Ø 1.6 - 2.1	1p	709176001511006	069176702001000	069176701901000	069176701801000	609176001521100	609176001521000
22	Ø 1.1 - 1.6	1p	709176001522006	069176702002000	069176701902000	069176701801000	609176001516100	609176001516000
24	Ø 1.1 - 1.6	1p	709176001532006	069176702002000	069176701902000	069176701801000	609176001516100	609176001516000
	* Hand Insertion Tooling and Cap Application - Universal Hand Tool 067000773001000; Consult Application Notes 201-01-124							


Certification: UL File #E90723





9176-500





CONTACT DETAILS












- 1. CONNECTOR FOR IDC WIRE TO BOARD CONNECTION.
- 2. CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3. CONTACT PLATING: PURE TIN.
- 4. CONNECTOR DESIGNED TO ACCEPT BETWEEN 18 AND 24 GAUGE STRANDED WIRE. SEE TABLE.
- 5. ALL DIMENSIONS FOR REFERENCE UNLESS OTHERWISE STATED.
- 6. FOR FULL PRODUCT SPECIFICATION REFER TO ELCO SPEC 201-01-106 AND APPLICATION NOTES 201-01-124.
- 7. SMT PCB LAYOUT, REFER TO PAGE 3.
- 8. PACKING IN TAPE AND REEL, QUANTITY 1000 PER REEL.
- 9. WHEN REQUIRED, MATCHING CAP DETAILS ON DRAWING 60-9176-001-5XX-X00S.
- 10. ASSEMBLY TOOLING ON PAGE 5 (WITH CAP AND WITHOUT CAP).









18-24 AWG IDC WIRE TO BOARD CONNECTOR SINGLE CONTACT

SMT PCB LAYOUT


PURE TIN PADS





ORIENTATION OF CONTACT ON PAD

ASSEMBLED/INSTALLED PRODUCTS



NOTES:


- 1. CONNECTOR CAN BE USED WITH CONTACT ONLY OR WITH OPTIONAL CAP.
- 2. OUTLINE OF CAP WHEN USED.
- 3. FOR FULL PRODUCT SPECIFICATION REFER TO ELCO SPEC 201-01-106 AND 201-01-124.
- 4. DIMENSIONS SHOWN ARE REFERENCED DIMENSIONS.
- 5. ASSEMBLY TOOLING ON PAGE 43 (WITH CAP AND WITHOUT CAP).



9176-500



ASSEMBLY TOOLING - CAP USED




CAP APPLICATION TOOL

06-9176-7018-01-000

UNIVERSAL HANDLE


06 7000 7730 01 000



NOTES:

- 1. ASSEMBLY TOOLING FOR CAP.
- 2. AREA OF PCB TO BE KEPT CLEAR OF COMPONENTS, TACKS PERMISSIBLE.
- 3. WIRE AND CAP INSERTED IN ONE OPERATION.
- 4. REFER TO APPLICATION NOTE 201-01-124 FOR FURTHER INFORMATION.
- 5. REFER BELOW WHEN CONTACT USED WITHOUT CAP.


ASSEMBLY TOOLING - CAP NOT USED WIRE ONTO CONTACT



- 1. ASSEMBLY TOOLING FOR CONTACT ONLY, NO CAP USED.
- 2. MINIMUM AREA OF PCB TO BE KEPT CLEAR OF COMPONENTS, TRACK PERMISSIBLE.
- 3. REFER TO TABLE FOR CORRECT TOOL/WIRE COMBINATION.
- 4. REFER TO APPLICATION NOTE 201-01-124 FOR FURTHER INFORMATION.

2.1 WIRE (18-20 AWG)


06-9176-7019-01-000 06-9176-7020-01-000




1.6 WIRE (22-24 AWG) 06-9176-7019-02-000

ORIENTATE CAP IN TOOL

06-9176-7020-02-000



UNIVERSAL HANDLE




Wire Guage	Wire Insulation ø	Metal Tool High Volume	Plastic Tool Small to Medium Volume	Handle
22-24 AWG	1.10 to 1.60	06-9176-7019-02-000	06-9176-7020-02-000	06-7000-7730-01-000
18-20 AWG	1.60 to 2.10	06-9176-7019-01-000	06-9176-7020-01-000	06-7000-7730-01-000




9176-500





CAP DETAILS











Code	Insulator Diameter (AWG)	В	Text C
516	1.1 to 1.6 (22-24)	1.00	Ø 1.6
521	1.6 to 2.1 (18-20)	1.50	Ø 2.1

NOTES:

- 1. CAP FOR IDC WIRE TO BOARD CONNECTION.
- 2. CAP MATERIAL: GLASS FILLED NYLON 46, COLOR SEE PAGE 1.
- 3. CAPS DESIGNED TO ACCOMMODATE WIRE INSULATION DIAMETERS 1.1MM TO 2.1MM.
- 4. ALL DIMENSIONS FOR REFERENCE UNLESS OTHERWISE STATED.
- 5. FOR FULL PRODUCT SPECIFICATION REFER TO ELCO SPEC 201-01-106, APPLICATION NOTES 201-01-124.
- 6. PACKING IN BAGS, QUANTITY 1000 PER BAG.
- 7. FOR INSTALATION DETAILS REFER TO DRAWING 70-9176-001-XX-006S.

