



AMPHENOL P/N	PCB THICKNESS	DIM "A"	DIM 'A'	DIM 'B'
HE11-RDA-110-3	.062"[1.57]	.053"[1.35]	.053±.01"[1.35±0.25mm]	
HE11-RDA-110-3-C	.062"[1.57]	.053"[1.35]	.053±.01"[1.35±0.25mm]	
HE11-RDA-110-3-CT	.062"[1.57]	.053"[1.35]	.053±.01"[1.35±0.25mm]	
HE11-RDA-110-4	.093"[2.36]	.081"[2.05]	.064±.01"[1.62±0.25mm]	
HE11-RDA-110-4-C	.093"[2.36]	.081"[2.05]	.064±.01"[1.62±0.25mm]	
HE11-RDA-110-4-CT	.093"[2.36]	.081"[2.05]	.064±.01"[1.62±0.25mm]	

HE 11 - RDA - 110 - X - XX

OPTIONS: _____
 3= FOR 0.062" THICK PCB
 4= FOR 0.093" THICK PCB

BLANK= WITHOUT PLUG & WITH TUBE PACKAGING;
C = WITH PLUG & TUBE PACKAGING;
CT= WITH PLUG & TAPE & REEL PACKAGING

2		1	
REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	PROPOSAL DRAWING	MAY 30/05	KL
B	ECN E07376	Oct 22/03	LOHAN
C	CHANGE DIM FROM 0.031(0.80) TO 0.0315(0.80)	MAY 18/09	AG



NOTE:

PLASTIC HOUSING: GLASS FILLED THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0.
COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE



30 u" [0.76 MICRONS] GOLD OVER
50 u" [1.27 MICRONS] NICKEL.
150 u"~ 300U" [3.75~7.50 MICRONS]
MATTE TIN OVER NICKEL IN SOLDER TAIL AREA.

SHELL: STEEL, NICKEL PLATED.

GROUNDING CLIP: COPPER ALLOY , 150u" (3.75 MICRONS)
MATTE TIN OVER 50u" (1.27 MICRONS) NICKEL

REFLOW: 6u" (0.15 MICRONS) MIN. SOLDER PASTE ON
P.C. BOARD REQUIRED FOR REFLOW PROCESS.

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE
OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.




UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	APPROVALS		DATE		Amphenol Canada Corp. TITLE VHDCI STRADDLE MOUNT RECEPTACLE, NO SCREWLOCKS, SHIELDED WITH NO EMI TABS RDS COMPLIANT					
	DRAWN	L.CHAN	MAY 30.05							
	DESIGNED									
	CHECKED	K.LAMBIE	MAY 30.05							
MATERIAL AND FINISH	SEE NOTES									
REF.	ECN E07376				SIZE	ING. NO.	P-HE11-RDA-110-X-XX		REV.	C
CAGE IDENT. NO.	03554				SCALE	2 = 1	PROJECT	RDA	SHEET	1 OF 2

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	PROPOSAL DRAWING	MAY 30/05	KL
B	ECN E07376	OCT 22/03	LCHN
C	CHANGE DIM FROM 0.031(0.80) TO 0.0315(0.80)	MAY 18/09	AG




TOP VIEW
(COVER TAPE NOT SHOWN)
(SHOWN WITH HE11-RDA-110-X-CT)

SEE DETAIL 'A'




TAPE AND REEL PACKAGING DETAIL
REEL WITH CARRIER TAPE & COVER
REEL NOT EXACTLY AS SHOWN




DETAIL 'A'
SCALE 2:1

SECTION 'B-B'




FINISHED CONNECTOR
(HE11-RDA-110-X-CX SHOWN)



TOP VIEW
(HE11-RDA-110-X-CX SHOWN)

PLUG COVER TO BE
REMOVED AFTER
CONNECTOR SOLDERED
INTO THE PCB



FRONT VIEW
(PLUG COVER NOT SHOWN)



PACKAGING NOTES:

- REEL DETAILS:
 - O.D.: 330.00 [12.992].
 - THICKNESS: 56.8 [2.236].
 - CONNECTORS PER REEL: 496.
- TAPE & REEL PACKAGING IS IN COMPLIANCE WITH EIA 481.

DO NOT SCALE DRAWING
OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	APPROVALS		DATE		Amphenol Canada Corp.						
	DRAWN	L.CHAN	MAY 30.05								
	DESIGNED				TITLE VHDCI STRADDLE MOUNT RECEPTACLE, NO SCREWLOCKS, SHIELDED WITH NO EMI TABS RoHS COMPLIANT						
	CHECKED		K.LAMBIE								
INTERNAL AND FINISH		BY APPR		MAY 30.05							
SEE NOTES											
REF.	ECN E07376		BY APPR				SIZE B	DWG NO.	P-HE11-RDA-110-X-XX	REV.	C
CODE IDENT. NO.	03554		DWG APPR				SCALE	2 = 1		PROJECT	RDA
							SHEET	2 OF 2			