



Main

| | |
|-------------------------------|--|
| Range of product | Harmony XVB Universal |
| Product or component type | Complete beacon |
| Beacon/Indicator bk unit type | Illuminated unit Base unit with direct or tube fixing mode |
| Signalling type | Flashing |
| Mounting diameter | 70 mm |
| Component name | XVBL |
| Material | Polycarbonate (illuminated unit) Glass reinforced polyamide (base unit) |
| Light source | Orange integral flash discharge tube |
| Bulb type | Flash discharge tube |
| [Us] rated supply voltage | 230 V AC |

Complementary


| | |
|--|--|
| Connections - terminals | Screw clamp terminals, connection capacity: ≤ 1 x 1.5 mm ² with cable end |
| [Ui] rated insulation voltage | 250 V conforming to IEC 60947-1 |
| Nominal voltage limit | 0.85...1.1 Un conforming to IEC 60947-5-1 |
| Current consumption | < 280 mA AC |
| [Uimp] rated impulse withstand voltage | 4 kV conforming to IEC 60947-1 |
| Flash energy | 10 J |
| Flashing frequency | 1 Hz |
| CAD overall width | 70 mm |
| CAD overall height | 232 mm |
| CAD overall depth | 70 mm |
| Terminals description ISO n°1 | (COM-1)PW (GND)GROUND |
| Product weight | 0.46 kg |

Environment

| | |
|--|--|
| Product certifications | CCC CSA C22-2 No 14 GOST UL 508 |
| Standards | EN/IEC 60947-5-1 |
| Protective treatment | TC |
| Ambient air temperature for storage | -40...70 °C |
| Class of protection against electric shock | Class II (on base unit) conforming to IEC 61140 Class I (on support tube) conforming to IEC 61140 |
| IP degree of protection | IP66 (on base unit) conforming to IEC 60529 IP65 (on fixing base XVBZ0.) conforming to IEC 60529 |
| NEMA degree of protection | NEMA 4X (indoor) conforming to UL 508 |

Illuminated Beacon with "Flash" Discharge Tube Unit

Dimensions



Illuminated Beacon

Wiring Diagram

