

## Short circuit proof PCB transformer **APT 7,5/2/15**



### Advantages

- Minimum size at high output
- Integrated overload protection using PTC in the input
- Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDensiFill resin encapsulation
- Coil shell in 2-chamber technology
- Self-extinguishing potting material
- Space saving installation thanks to additional screw mounting in the base plate

### Applications

As a safety transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

### Standards




Safety isolating transformer  
to: VDE 0570 Part 2-6, DIN EN 61558-2-6, EN 61558-2-6, IEC 61558-2-6,  
UL 5085-1/-2, CSA 22.2 No.66

### Approvals



ENEC 10 (VDE), UL 5085-1/-2, CSA 22.2 No.66



## Short circuit proof PCB transformer APT 7,5/2/15

Type		APT 7,5/2/15
Electrical data	Input	
	Rated input Voltage	115 Vac
	Rated frequency	50 - 60 Hz
	Output	
	Rated output voltage	2 x 15 Vac
	Rated Power	7.5 VA
	No-load voltage (app. x factor)	1.21
	No-load loss (typ.)	1.30 W
	Efficiency	65 %
	Standards	
	Classification	Safety isolating transformer
	Approvals	
	Approvals	cURus, ENEC (VDE)
	Environment	
	Ambient temperature max.	40 °C
	Safety and protection	
	Type	encapsulated
	Class of Insulation System	VDE=B, UL=class 105
	Protection index	IP 00
Safety class (prepared)	II	
Short circuit strength	non-inherently short-circuit proof	
Order numbers		
<b>Order Number</b>	<b>APT 7,5/2/15</b>	

Type		APT 7,5/2/15
Mechanical data	Terminal and mounting	
	Terminals	Pins for printed circuit boards
	Measures and weights	
	Dimension (W x H x D)	
	Pin (ø)	0.8 mm
Core type	EI 48/16,8	
Weight	0.28 kg	

Subjects to change.