


# RF3934

## 120W GaN Wideband Power Amplifier

The RF3934 is a 48V 120W high power discrete amplifier designed for commercial wireless infrastructure, cellular and WiMAX infrastructure, industrial/scientific/medical and general purpose broadband amplifier applications. Using an advanced high power density Gallium Nitride (GaN) semiconductor process, these high-performance amplifiers achieve high efficiency and flat gain over a broad frequency range in a single amplifier design. The RF3934 is an unmatched GaN transistor packaged in a hermetic, flanged ceramic package. This package provides excellent thermal stability through the use of advanced heat sink and power dissipation technologies. Ease of integration is accomplished through the incorporation of simple, optimized matching networks external to the package that provide wideband gain and power performance in a single amplifier.



Functional Block Diagram

### Ordering Information

|                |   |
|----------------|---|
| RF3934S2       | Sample bag with 2 pieces                                    |
| RF3934SB       | Bag with 5 pieces   |
| RF3934SQ       | Bag with 25 pieces  |
| RF3934SR       | Short Reel with 50 pieces                                   |
| RF3934TR13     | 13" Reel with 400 pieces                                    |
| RF3934PCBA-411 | Fully assembled evaluation board optimized for 2.14GHz; 48V |



Package: Hermetic, 2-Pin, Flanged Ceramic

### Features

- Broadband Operation DC to 3.5GHz
- Advanced GaN HEMT Technology
- Advanced Heat-Sink Technology
- Small Signal Gain = 13dB at 2GHz
- 48V Operation Typical Performance
  - Output Power: 140W at P3dB
  - Drain Efficiency = 60% at P3dB
  - -40°C to 85°C Operation

### Applications

- Commercial Wireless Infrastructure
- Cellular and WiMAX Infrastructure
- Civilian and Military Radar
- General Purpose Broadband Amplifiers
- Public Mobile Radios
- Industrial, Scientific, and Medical

## Absolute Maximum Ratings

| Parameter   | Rating      | Unit  |
|---|-------------|-------|
| Drain Voltage ( $V_D$ )   | 150         | V     |
| Gate Voltage ( $V_G$ )  | -8 to +2    | V     |
| Gate Current ( $I_G$ )  | 78          | mA    |
| Operational Voltage   | 65          | V     |
| Ruggedness (VSWR)   | 10:1        |       |
| Storage Temperature Range   | -55 to +125 | °C    |
| Operating Temperature Range ( $T_C$ )   | -40 to +85  | °C    |
| Operating Junction Temperature ( $T_J$ )  | 200         | °C    |
| Human Body Model  | Class 1A    |       |
| MTTF ( $T_J < 200^\circ\text{C}$ , 95% Confidence Limits)*  | 1.8E + 07   | Hours |
| MTTF ( $T_J < 250^\circ\text{C}$ , 95% Confidence Limits)*  | 1.1E + 05   |       |
| Thermal Resistance, $R_{TH}$ (junction to case) measured at $T_C = 85^\circ\text{C}$ , DC bias only | 1.6         | °C/W  |



**Caution!** ESD sensitive device.



RFMD Green: RoHS compliant per EU Directive 2011/65/EU, halogen free per IEC 61249-2-21, <1000ppm each of antimony trioxide in polymeric materials and red phosphorus as a flame retardant, and <2% antimony solder.

Exceeding any one or a combination of the Absolute Maximum Rating conditions may cause permanent damage to the device. Extended application of Absolute Maximum Rating conditions to the device may reduce device reliability. Specified typical performance or functional operation of the device under Absolute Maximum Rating conditions is not implied.

\* MTTF – Median time to failure as determined by the process technology wear-out failure mode. Refer to product qualification report for FIT (random) failure rate.

Operation of this device beyond any one of these limits may cause permanent damage. For reliable continuous operation, the device voltage and current must not exceed the maximum operating values specified in the table above.







Bias Conditions should also satisfy the following expression:  $P_{DISS} < (T_J - T_C) / R_{TH\ J-C}$  and  $T_C = T_{CASE}$

## Nominal Operating Parameters






| Parameter                                    | Specification |      |      | Unit | Condition               |
|--|---------------|------|------|------|-------------------------|
|  | Min           | Typ  | Max  |      |                         |
| <b>Recommended Operating Conditions</b>      |               |      |      |      |                         |
| Drain Voltage ( $V_{DSQ}$ )                  | 28            |      | 48   | V    |                         |
| Gate Voltage ( $V_{GSQ}$ )                   | -4.5          | -3.7 | -2.5 | V    |                         |
| Drain Bias Current                           |               | 440  |      | mA   |                         |
| Frequency of Operation                       | DC            |      | 3500 | MHz  |                         |
| <b>Capacitance</b>                           |               |      |      |      |                         |
| $C_{RSS}$                                    |               | 9    |      | pF   | $V_G = -8V, V_D = 0V$   |
| $C_{ISS}$                                    |               | 40   |      | pF   |                         |
| $C_{OSS}$                                    |               | 27.5 |      | pF   |                         |
| <b>DC Functional Test</b>                    |               |      |      |      |                         |
| $I_{G(OFF)}$ - Gate Leakage                  |               |      | 2    | mA   | $V_G = -8V, V_d = 0V$   |
| $I_{D(OFF)}$ - Drain Leakage                 |               |      | 2.5  | mA   | $V_G = -8V, V_d = 48V$  |
| $V_{GS(TH)}$ - Threshold Voltage             |               | -4.2 |      | V    | $V_D = 48V, I_D = 20mA$ |
| $V_{DS(ON)}$ - Drain Voltage at High Current |               | 0.25 |      | V    | $V_G = 0V, I_D = 1.5A$  |

| Parameter   | Specification |       |     | Unit | Condition                            |
|---|---------------|-------|-----|------|--------------------------------------|
|   | Min           | Typ   | Max |      |                                      |
| <b>RF Functional Test</b>   |               |       |     |      |                                      |
| $V_{GSQ}$   |               | -3.4  |     | V    | $V_D = 48V, I_D = 440mA$             |
| Gain  | 10            | 12    |     | dB   | CW, $P_{OUT} = 50.8dBm, f = 2140MHz$ |
| Drain Efficiency  | 55            | 60    |     | %    |                                      |
| Input Return Loss   |               | -12   |     | dB   |                                      |
| <b>RF Typical Performance</b>   |               |       |     |      |                                      |
| <b>Test Conditions: CW operation, <math>V_{DSQ} = 48V, I_{DQ} = 440mA, T = 25^{\circ}C</math>, Performance in a standard tuned test fixture</b> |               |       |     |      |                                      |
| Small Signal Gain   |               | 21    |     | dB   | CW, $f = 900MHz$                     |
|   |               | 13    |     | dB   | CW, $f = 2140MHz$                    |
| Output Power at P3dB  |               | 51.60 |     | dBm  | CW, $f = 900MHz$                     |
|   |               | 51.46 |     | dBm  | CW, $f = 2140MHz$                    |
| Drain Efficiency at P3dB  |               | 75    |     | %    | CW, $f = 900MHz$                     |
|   |               | 60    |     | %    | CW, $f = 2140MHz$                    |







**Typical Performance in Standard 2.14GHz Tuned Test Fixture**  
(CW, T = 25°C, unless noted)





**Typical Performance in Standard 2.14GHz Tuned Test Fixture**  
(CW, T = 25°C, unless noted) (continued)




**Typical Performance in Standard 900MHz Tuned Test Fixture**  
(CW, T = 25°C, unless noted)



**Typical Performance in Standard 900MHz Tuned Test Fixture**  
 (CW, T = 25°C, unless noted) (continued)



## Package Drawing (Package Style: Flanged Ceramic)




## Pin Names and Descriptions


| Pin | Name   | Description          |
|-----|--------|----------------------|
| 1   | GATE   | Gate - VG Input      |
| 2   | DRAIN  | Drain - VD RF Output |
| 3   | SOURCE | Source - Ground Base |

## Bias Instruction for RF3934 Evaluation Board

- ESD Sensitive Material. Please use proper ESD precautions when handling devices of evaluation board.
  - Evaluation board requires additional external fan cooling.
  - Connect all supplies before powering up the evaluation board.
1. Connect RF cables at RFIN and RFOUT.
  2. Connect ground to the ground supply terminal, and ensure that both the VG and VD grounds are also connected to this ground terminal.
  3. Apply -8V to VG.
  4. Apply 48V to VD.
  5. Increase  $V_G$  until drain current reaches desired 440mA bias point.
  6. Turn on RF input.




## 2.14GHz Evaluation Board Schematic



## 2.14GHz Evaluation Board Bill of Materials (BOM)

| Item              | Value                           | Manufacturer | Manufacturer's P/N |
|-------------------|---------------------------------|--------------|--------------------|
| C1                | 10pF                            | ATC          | ATC800A100JT       |
| C2, C10, C11, C15 | 33pF                            | ATC          | ATC800A330JT       |
| C3, C14           | 0.1μF                           | Murata       | GRM32NR72A104KA01L |
| C4, C13           | 4.7μF                           | Murata       | GRM55ER72A475KA01L |
| C5                | 100μF                           | Panasonic    | ECE-V1HA101UP      |
| C6                | 2.0pF                           | ATC          | ATC800A2R0BT       |
| C7                | 0.3pF                           | ATC          | ATC800A0R3BT       |
| C8                | 1.5pF                           | ATC          | ATC800A1R5BT       |
| C9                | 2.7pF                           | ATC          | ATC800A2R7BT       |
| C12               | 100μF                           | Panasonic    | EEV-TG2A101M       |
| C17               | 1.8pF                           | ATC          | ATC800A1R8BT       |
| R1                | 10Ω                             | Panasonic    | ERJ-8GEYJ100V      |
| C16, C18, C19     | Not used                        | -            | -                  |
| PCB               | RO4350, 0.030" thick dielectric | Rogers       | -                  |


### 2.14GHz Evaluation Board Layout




### Device Impedances

| Frequency (MHz) | Z Source ( $\Omega$ ) | Z Load ( $\Omega$ ) |
|-----------------|-----------------------|---------------------|
| 2110            | 1.58 - j2.56          | 3.5 - j0.08         |
| 2140            | 1.49 - j2.25          | 3.46 + j0.38        |
| 2170            | 1.42 - j1.96          | 3.43 + j0.85        |

**Note:** Device impedances reported are the measured evaluation board impedances chosen for a tradeoff of efficiency, peak power, and linearity performance across the entire frequency bandwidth.




## 900MHz Evaluation Board Schematic



## 900MHz Evaluation Board Bill of Materials (BOM)

| Item             | Value         | Manufacturer | Manufacturer's P/N |
|------------------|---------------|--------------|--------------------|
| C1, C2, C10, C11 | 68pF          | ATC          | ATC800A680JT       |
| C3, C14          | 0.1μF         | Murata       | GRM32NR72A104KA01L |
| C4, C13          | 4.7μF         | Murata       | GRM55ER72A475KA01L |
| C15              | Not Populated |              |                    |
| C6               | 15pF          | ATC          | ATC800A150JT       |
| C7               | 22pF          | ATC          | ATC800A220JT       |
| C8               | 12pF          | ATC          | ATC800A120JT       |
| C9               | 2.2pF         | ATC          | ATC800A2R2BT       |
| C12              | 330μF         | Panasonic    | EEU-FC2A331        |
| C5               | 100μF         | Panasonic    | ECE-V1HA101UP      |
| R1               | 10Ω           | Panasonic    | ERJ-8GEYJ100V      |


## 900MHz Evaluation Board Layout



## Device Impedances

| Frequency (MHz) | Z Source ( $\Omega$ ) | Z Load ( $\Omega$ ) |
|-----------------|-----------------------|---------------------|
| 880             | $1.24 + j3.0$         | $5.49 + j3.4$       |
| 900             | $1.14 + j3.63$        | $5.27 + j3.9$       |
| 920             | $1.11 + j4.20$        | $5.03 + j4.40$      |

**Note:** Device impedances reported are the measured evaluation board impedances chosen for a tradeoff of efficiency, peak power, and linearity performance across the entire frequency bandwidth.



## Device Handling/Environmental Conditions

GaN HEMT devices are ESD sensitive materials. Please use proper ESD precautions when handling devices or evaluation boards.

## GaN HEMT Capacitances

The physical structure of the GaN HEMT results in three terminal capacitors similar to other FET technologies. These capacitances exist across all three terminals of the device. The physical manufactured characteristics of the device determine the value of the  $C_{DS}$  (drain to source),  $C_{GS}$  (gate to source) and  $C_{GD}$  (gate to drain). These capacitances change value as the terminal voltages are varied. RFMD presents the three terminal capacitances measured with the gate pinched off ( $V_{GS} = -8V$ ) and zero volts applied to the drain. During the measurement process, the parasitic capacitances of the package that holds the amplifier is removed through a calibration step. Any internal matching is included in the terminal capacitance measurements. The capacitance values presented in the typical characteristics table of the device represent the measured input ( $C_{ISS}$ ), output ( $C_{OSS}$ ), and reverse ( $C_{RSS}$ ) capacitance at the stated bias voltages. The relationship to three terminal capacitances is as follows:

$$C_{ISS} = C_{GD} + C_{GS}$$

$$C_{OSS} = C_{GD} + C_{DS}$$

$$C_{RSS} = C_{GD}$$

## DC Bias

The GaN HEMT device is a depletion mode high electron mobility transistor (HEMT). At zero volts  $V_{GS}$  the drain of the device is saturated and uncontrolled drain current will destroy the transistor. The gate voltage must be taken to a potential lower than the source voltage to pinch off the device prior to applying the drain voltage, taking care not to exceed the gate voltage maximum limits. RFMD recommends applying  $V_{GS} = -5V$  before applying any  $V_{DS}$ .

RF Power transistor performance capabilities are determined by the applied quiescent drain current. This drain current can be adjusted to trade off power, linearity, and efficiency characteristics of the device. The recommended quiescent drain current ( $I_{DQ}$ ) shown in the RF typical performance table is chosen to best represent the operational characteristics for this device, considering manufacturing variations and expected performance. The user may choose alternate conditions for biasing this device based on performance trade-offs.

## Mounting and Thermal Considerations

The thermal resistance provided as  $R_{TH}$  (junction to case) represents only the packaged device thermal characteristics. This is measured using IR microscopy capturing the device under test temperature at the hottest spot of the die. At the same time, the package temperature is measured using a thermocouple touching the backside of the die embedded in the device heat-sink but sized to prevent the measurement system from impacting the results. Knowing the dissipated power at the time of the measurement, the thermal resistance is calculated.