

## Material Declaration for R30-300XX02

Product Information	
Part Number:	R30-300XX02
Part Description:	M3 M/F Spacer
Part Weight (g):	See table

Process Data	
Peak Reflow (Deq. C)	Not applicable
MSL	1
Lead Finish	Not applicable
RoHS Compliant Mark	n/a
Availability Date	Now
RoHS Compliant? (Y/N)	Yes

Part Number	Part Weight (g)	Base Material - Brass								Plating	Homogeneous Material Location
		Copper	Zinc	Lead	Iron	Tin	Nickel	Aluminium	Impurities	Nickel	Substance Name
		7440-50-8	7440-66-6	7439-92-1	7439-89-6	7440-31-5	7440-02-0	7429-90-5		7440-02-0	CAS #
		3	3	2	Max	Max	Max	Max	Max	20	Tolerance (%)
		Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	Weight (g)	
R30-3000402	0.866	0.5	0.336	0.026	0.0026	0.0026	0.0026	0.00043	0.0017	0.0039	
R30-3000502	1.024	0.592	0.398	0.031	0.0031	0.0031	0.0031	0.00051	0.002	0.0043	
R30-3000602	1.16	0.67	0.45	0.035	0.0035	0.0035	0.0035	0.00058	0.0023	0.0048	
R30-3000702	1.288	0.744	0.5	0.038	0.0038	0.0038	0.0038	0.00064	0.0026	0.0054	
R30-3000802	1.421	0.821	0.552	0.042	0.0042	0.0042	0.0042	0.00071	0.0028	0.006	
R30-3000902	1.556	0.899	0.605	0.047	0.0047	0.0047	0.0047	0.00078	0.0031	0.0064	
R30-3001002	1.718	0.992	0.667	0.051	0.0051	0.0051	0.0051	0.00086	0.0034	0.0068	
R30-3001102	1.857	1.073	0.722	0.056	0.0056	0.0056	0.0056	0.00093	0.0037	0.0073	
R30-3001202	2.041	1.179	0.793	0.061	0.0061	0.0061	0.0061	0.00102	0.0041	0.0076	
R30-3001302	2.224	1.285	0.864	0.066	0.0066	0.0066	0.0066	0.00111	0.0044	0.0079	
R30-3001402	2.407	1.391	0.936	0.072	0.0072	0.0072	0.0072	0.0012	0.0048	0.0082	
R30-3001502	2.591	1.498	1.007	0.077	0.0077	0.0077	0.0077	0.00129	0.0052	0.0085	
R30-3001602	2.774	1.604	1.078	0.083	0.0083	0.0083	0.0083	0.00138	0.0055	0.0088	
R30-3001702	2.957	1.71	1.15	0.088	0.0088	0.0088	0.0088	0.00147	0.0059	0.0091	
R30-3001802	3.14	1.816	1.221	0.094	0.0094	0.0094	0.0094	0.00157	0.0063	0.0094	
R30-3001902	3.324	1.922	1.292	0.099	0.0099	0.0099	0.0099	0.00166	0.0066	0.0097	
R30-3002002	3.507	2.028	1.364	0.105	0.0105	0.0105	0.0105	0.00175	0.007	0.01	
R30-3002102	3.69	2.134	1.435	0.11	0.011	0.011	0.011	0.00184	0.0074	0.0103	
R30-3002202	3.874	2.241	1.507	0.116	0.0116	0.0116	0.0116	0.00193	0.0077	0.0106	
R30-3002402	4.24	2.453	1.649	0.127	0.0127	0.0127	0.0127	0.00212	0.0085	0.0112	
R30-3002502	4.424	2.559	1.721	0.132	0.0132	0.0132	0.0132	0.00221	0.0088	0.0115	
R30-3002602	4.607	2.665	1.792	0.138	0.0138	0.0138	0.0138	0.0023	0.0092	0.0118	
R30-3003002	5.34	3.09	2.078	0.16	0.016	0.016	0.016	0.00266	0.0107	0.013	
R30-3003202	5.707	3.302	2.22	0.171	0.0171	0.0171	0.0171	0.00285	0.0114	0.0136	
R30-3003402	6.072	3.514	2.363	0.182	0.0182	0.0182	0.0182	0.00303	0.0121	0.0142	
R30-3003502	6.256	3.62	2.434	0.187	0.0187	0.0187	0.0187	0.00312	0.0125	0.0145	
R30-3003802	6.805	3.938	2.648	0.204	0.0204	0.0204	0.0204	0.0034	0.0136	0.0154	
R30-3004002	7.172	4.15	2.791	0.215	0.0215	0.0215	0.0215	0.00358	0.0143	0.016	
R30-3004502	8.089	4.681	3.148	0.242	0.0242	0.0242	0.0242	0.00404	0.0161	0.0175	
R30-3005002	9.005	5.212	3.505	0.27	0.027	0.027	0.027	0.00449	0.018	0.0191	
R30-3006002	10.838	6.273	4.218	0.324	0.0324	0.0324	0.0324	0.00541	0.0216	0.0221	
R30-3008002	14.503	8.396	5.645	0.434	0.0434	0.0434	0.0434	0.00724	0.029	0.0281	

Prepared by:



Miss Wendy Jane Bourne, BEng  
RoHS Compliance Project Manager  
leadfree@harwin.co.uk

On behalf of:

