


### INTRODUCTION

Wamco LED Stick series BL05-I is a linear lighting system for direct & indirect accent lighting applications such as building alcoves, shelves, sculptures, etc. The BLO5-I system is also designed for side lighting of sign panels in both indoor and outdoor installations. BL05-I is available in white and warm white in 300, 600, 900 and 1200mm lengths. BL05-I provides many advantages including brilliant light output, significant energy savings and reduced maintenance costs.



### **FEATURES**

- Mounted via affixed brackets or mounting clips
- Two color options (white-6000K / warm-white-3000K)
- Four length options (300mm / 600mm / 900mm / 1200mm)
- Water resistant (outdoor use, IP65)
- Long life time (up to 40,000 hours)
- Safety due to low working voltage (24VDC)
- 3 year warranty



- Accent lighting (building, bridge, etc.)
- Indoor and outdoor decorative lighting




CE, RoHS












#### **SPECIFICATIONS**

MODEL	COLOR	LENGTH	LED QUANTITY	INPUT VOL.	POWER	VIEW ANGLE	LUM.FLUX
WL-B05I03W0300	White (Typ.6000K)	337mm	18 pieces	24VDC	2.9W	120°	248lm
WL-B05I06W0600	White (Typ.6000K)	638mm	36 pieces	24VDC	5.8W	120°	496lm
WL-B05I09W0900	White (Typ.6000K)	939mm	54 pieces	24VDC	8.7W	120°	744lm
WL-B05I12W1200	White (Typ.6000K)	1239mm	72 pieces	24VDC	11.6W	120°	992lm
WL-B05I03L0300	Warm-White (Typ.3000K)	337mm	18 pieces	24VDC	2.9W	120°	230lm
WL-B05I06L0600	Warm-White (Typ.3000K)	638mm	36 pieces	24VDC	5.8W	120°	460lm
WL-B05I09L0900	Warm-White (Typ.3000K)	939mm	54 pieces	24VDC	8.7W	120°	690lm
WL-B05I12L1200	Warm-White (Typ.3000K)	1239mm	72 pieces	24VDC	11.6W	120°	920lm


CALL FAX **VISIT EMAIL** 1-714-545-5560 1-714-545-6093 W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM



## PHYSICAL SPECIFICATION (unit: mm)



### LIGHT DISTRIBUTION



BL05I\_White\_300mm (6000K/18LEDs)

CALL 1-714-545-5560 FAX 1-714-545-6093

VISIT

**EMAIL** 

W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM



### INSTALLATION

☑ Before you begin

- Lighting must be installed by a qualified electrician in according with all national and local electrical regulations
- Determine proper placement in relation to the size and complexity of your installation
- Make sure Power is off before installation and follow installation process.
- 1. Install using screws and the brackets on each end of the stick




2. Or using mounting clips








3. Connect additional fixtures using connector cable







Please note that a positive pole (+) and a negative pole (-) should be connected in the same lines when you connect additional fixtures. If the connection is not correct, BL05 will not work properly.



CALL 1-714-545-5560 FAX

1-714-545-6093

VISIT


W: WWW.WAMCOINC.COM


EMAIL

E: INFO@WAMCOINC.COM



4. Connect DC power supply (24VDC output) using leader cable





### **CAPACITY TABLE**

LENGTH	WATT	DC POWER SUPPLY MAX NUMBER CONNECTED			
(unit: mm)	(a piece)	100W	300W		
WL-B05I300mm	2.9W	24 pieces	72 pieces		
WL-B05I600mm	5.8W	12 pieces	36 pieces		
WL-B05I900mm	8.7W	8 pieces	24 pieces		
WL-B05I1200mm	11.6W	6 pieces	18 pieces		



- Ensure main power supply is off before installing or wiring fixtures.
- Do not exceed the specified voltage and current input for any fixtures.
- 5. Turn on the power. Check to see if BL05 lights.
  Please review all installation processes above if BL05 fails to light.



CALL 1-714-545-5560 FAX 1-714-545-6093 VISIT

W: WWW.WAMCOINC.COM

**EMAIL** 

E: INFO@WAMCOINC.COM




### **ACCESSORIES**

**CONNECTING CABLE** 

CONNECTING CABLE LENGTH MODEL NAME DESCRIPTION



### **PACKAGING**



WL-BL05I Rev 1 06/17/2013

W: WWW.WAMCOINC.COM