

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19199-0008

Status:

Active

Overview:

Splices

Description:

Avikrimp™ Window Butt Connector for 18-22 AWG Wire, Mylar Tape Carrier

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-015 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Splices

Series

19199

Comments

Mil Spec M7928/5-3

Crimp Quality Equipment

Yes

Mil-Spec

M7928/5-3

Overview

Splices

Product Name

Avikrimp™, Butt - Window

UPC

800753046818

Physical

Barrel Type

Closed

Color - Resin

Red

Insulation

Nylon (PA)

Material - Metal

Copper

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

1.194/g

Packaging Type

Adhesive Tape on Reel

Temperature Range - Operating

-55°C to +105°C

Wire Insulation Diameter

3.56mm max.

Wire Size AWG

18, 20, 22

Wire Size mm²

0.25 - 1.50

Electrical

Voltage - Maximum

300V

Material Info

Old Part Number

WA-840T

Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-015

Sales Drawing

SD-19199-003



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19199Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Mini-Mac Applicator	0638859100
Air Feed-Mylar Tape Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals	0192880043

This document was generated on 09/05/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION