

Panel feed-through - ST-5EP1N8ACK04S - 1618769

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Panel feed-through, straight, SPEEDCON locking, M17, Number of positions: 5+PE, Type of contact: Male connector, Crimp connection, Flat gasket, 4xØ3,2, shielded: Yes, Flange dimensions: 25.75 mm x 25.75 mm, Cable diameter: 9 mm...11 mm

The illustration shows the 4-position version



Key commercial data

Packing unit	1 pc
GTIN	4 046356 817301
Weight per Piece (excluding packing)	42.6 g
Custom tariff number	85366990
Country of origin	Germany
Product key	ABRCEK
Note	Made to Order (non-returnable)

Technical data

General

Note	Order information Order crimp contacts Ø 1 mm separately
Type of locking	SPEEDCON locking
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Crimp connection
Type of contacts	Male connector
Number of positions	6
Contact diameter of power contacts	1 mm
Nominal current per power contact at 25°C	14 A
Contact diameter of signal contacts	1 mm
Conductor entry	9 mm ... 11 mm
Mounting type	4xØ3,2

Ambient conditions

Panel feed-through - ST-5EP1N8ACK04S - 1618769

Technical data

Ambient conditions

Degree of protection	IP67
----------------------	------

Specifications according to DIN EN 61984:2001

Nominal / operating voltage of power contacts	630 V
Rated surge voltage of power contacts	6 kV
Surge voltage category of power contacts	III
Pollution degree of power contacts	3

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440103

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002061

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals

Approvals

UL Recognized / UL Recognized / cUL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Panel feed-through - ST-5EP1N8ACK04S - 1618769

Approvals

Approvals submitted

Approval details

UL Recognized	
mm ² /AWG/kcmil	1
Nominal current I _N	6 A
Nominal voltage U _N	600 V

UL Recognized	
mm ² /AWG/kcmil	1
Nominal current I _N	6 A
Nominal voltage U _N	600 V

cUL Recognized	
mm ² /AWG/kcmil	1
Nominal current I _N	6 A
Nominal voltage U _N	600 V

cUL Recognized	
mm ² /AWG/kcmil	1
Nominal current I _N	6 A
Nominal voltage U _N	600 V

cULus Recognized	
------------------	--

Drawings

Panel feed-through - ST-5EP1N8ACK04S - 1618769

Schematic diagram



Connector pin assignment

Dimensioned drawing

