


Capacitor, ceramic, 0.01 uF, +/-10% Tol, 100V, Ultra-Stable X8R dielectric



Dimensions (in)		
Symbol	Dimension	Tolerance
D	0.1	MAX
L	0.17	MAX
LL	1	MIN

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	0.01 uF
Temperature Coefficient:	Ultra-Stable X8R
Temperature Range:	-55°C to 150°C
Application:	Automotive
Voltage:	100V
Tolerance:	+/- 10%
Body Type:	Axial Conformal
Lead Type:	Standard Leads
Termination Type:	Tin (Sn)

Packaging Specifications	
Package Kind:	T&R
Package Type:	Standard
Package Quantity:	5000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.