





[Heatsink home](#)
[Contact technical sales](#)
[View another heatsink](#)
[Find another heatsink type](#)



Stock Category A. Profile normally held in stock and available on a short leadtime. Minimum order value of £100.00 may apply.



Thermal Performance Results	
Passive [°C/W]	1.100
Forced air flow [°C/W]	0.530

Interactive Performance Graph		
Enter new length [mm]	150	Default: 150
Enter new air flow [m/s]	2.00	Default: 2
<input type="button" value="Calculate"/>		
Click to update the graph and the Thermal Performance Results above		

Thermal Resistance is calculated based on a distributed heat load on anodised heatsink with vertically mounted fins based on a 60i½C temperature rise. Under general operating conditions the thermal mounting arrangement of devices is not known and therefore the figures should be used only as a guide to selection. We recommend that the effectiveness of any heatsink is tested in the specific operating environment in which it will be subjected. All information is for reference purposes only.