

# CXHDU850CS3





## Features:

- 1/3" SONY 720P CMOS Imager (Sony Imx238 plus Eyenix778)
- 1000TVL, min. illumination 0.01Lux/F1.2 (0Lux IR ON)
- Ultra Wide Dynamic Performance up to 115dB
- 2.8-12mm HD Lens
- 2 Year Warranty
- Surface or Flush Ceiling Fit (Both Included)
- IR Cut Filter
- DC12V
- Digital Zoom 1x-8 x/ Defog / Mirror / Shading / Privacy Masks / Sense up 50X

## Specifications

Image Sensor	1/3" SONY 720P CMOS Imager
Signal System	NTSC ; PAL
Effective Pixels	PAL:1280(H)x1024(V)
Resolution	1000TVL
SNR	≥50dB(AGC Off)
Min. Illumination	0.01Lux/F1.2(0Lux IR ON)
Scanning System	2:1 interlace scanning
Sync System	internal
Video Output	1.0Vp-p/75Ω
WDR	HI/MID/LOW/OFF
White Balance	Auto/Autoext/Preset/Manual
Backlight Compensation	BLC, OFF, HLC, WDR
Image Reverse	Mirror/brightness/contrast/tone/gain/sharpness
Motion Detection	on,off (settable)
Privacy Mask	on,off (settable)
DNR	HI/MID/LOW/OFF
Dimensions	108.5(H) * 170(Ø) mm
IR LED	20 pcs Smart IR LEDs
IR Range	20 Meters
Lens	2.8~ 12mm HD Lens
Input Voltage	DC12V±10%
Current	200mA
Shutter Speeds	AUTO/MANUAL(1/50 - 1/60,000 sec)
Weight	375g
IP Rating	IP66
Operation Temperature	-10 ~+50 (14 ~122 )
Operation Humidity	<90%RH(no condensation)

## Dimensions



## Applications:

- Banks and Building Society Branches
- Premium and General Retail
- Commercial Properties
- Industrial Parks and Factories
- General Law Enforcement
- Transport Hubs
- Premium Domestic Surveillance