



Twist drills DIN 338 type VA, in fractional sizes



Powerful right-hand cutting high-performance drill with distinctive heat resistance and **reinforced drill core**. Ideal for drilling high-strength stainless, acid-resistant and heat-resistant steel.

Packing unit: in plastic box



steel (N/mm ²)			stainless steel	aluminium	brass	bronze	plastics	cast iron	titanium alloyed
< 900	< 1100	< 1300							
●	●		●						○

● Main application

○ Other application

Ø inch	Ø mm	L1 in inch	L2 in inch	Article no. HSSE-Co5	Cont. pcs.	Article no. HSSE-Co5	Cont. pcs.
1/16	1,59	1 7/8	7/8	215 801	10	215 801 Z	10
5/64	1,98	2	1	215 802	10	215 802 Z	10
3/32	2,38	2 1/4	1 1/4	215 803	10	215 803 Z	10
7/64	2,78	2 5/8	1 1/2	215 804	10	215 804 Z	10
1/8	3,18	2 3/4	1 5/8	215 805	10	215 805 Z	10
9/64	3,57	2 7/8	1 3/4	215 806	10	215 806 Z	10
5/32	3,97	3 1/8	2	215 807	10	215 807 Z	10
11/64	4,37	3 1/4	2 1/8	215 808	10	215 808 Z	10
3/16	4,76	3 1/2	2 5/16	215 809	10	215 809 Z	10
13/64	5,16	3 5/8	2 7/16	215 810	10	215 810 Z	10
7/32	5,56	3 3/4	2 1/2	215 811	10	215 811 Z	10
15/64	5,95	3 7/8	2 5/8	215 812	10	215 812 Z	10
1/4	6,35	4	2 3/4	215 813	10	215 813 Z	10
17/64	6,75	4 1/8	2 7/8	215 814	10	215 814 Z	10
9/32	7,14	4 1/4	2 15/16	215 815	10	215 815 Z	10
19/64	7,54	4 3/8	3 1/16	215 816	10	215 816 Z	10
5/16	7,94	4 1/2	3 3/16	215 817	10	215 817 Z	10
21/64	8,33	4 5/8	3 5/16	215 818	10	215 818 Z	10
11/32	8,73	4 3/4	3 7/16	215 819	10	215 819 Z	10
23/64	9,13	4 7/8	3 1/2	215 820	10	215 820 Z	10
3/8	9,53	5	3 5/8	215 821	10	215 821 Z	10
25/64	9,92	5 1/8	3 3/4	215 822	10	215 822 Z	10
13/32	10,32	5 1/4	3 7/8	215 823	10	215 823 Z	10
27/64	10,72	5 3/8	3 15/16	215 824	5	215 824 Z	5
7/16	11,11	5 1/2	4 1/16	215 825	5	215 825 Z	5
29/64	11,51	5 5/8	4 3/16	215 826	5	215 826 Z	5
15/32	11,91	5 3/4	4 5/16	215 827	5	215 827 Z	5
31/64	12,30	5 7/8	4 3/8	215 828	5	215 828 Z	5
1/2	12,70	6	4 1/2	215 829	5	215 829 Z	5

Description	Article no. HSSE-Co5	Article no. HSSE-Co5
21-piece set of twist drills DIN 338 type VA, in fractional sizes Ø 1/16" up to 3/8" in increments of 1/64" in steel case	215 850	215 850 Z
29-piece set of twist drills DIN 338 type VA, in fractional sizes Ø 1/16" up to 1/2" in increments of 1/64" in steel case	215 851	215 851 Z