

Indoor Dome Camera



- 1/2.9" 1.0 Mega Pixels CMOS Sensor
- High rate, long-distance, real-time transmission
- Coaxial cable transmission technology, more than 500m via 75-3 cable
- Auto flickerless
- HD CVI output
- Power supply: DC12V

Specifications

Image Sensor	1/2.9" 1.0 Mega Pixels CMOS Sensor
Signal System	NTSC/PAL
Effective Pixels	1280(H)×720(V)
Min. Illumination	0.01Lux@ (F1.2, AGC ON)
Scanning System	Progressive
Synchronization	Internal
Frame Rate	50Hz:720p@25fps(1280×720) 60Hz:720p@30fps(1280×720)
Video Output	HD-CVI
Electronic Shutter	4/25s~1/450000s
Day&Night	Auto
White Balance	Auto
Backlight Compensation	Auto
IR LED	--/--
Lens	3.6mm/6mm
IR Range	--/--
Input Voltage	DC12V±10%
Current	90mA
Power Consumption	<2W
Weight	185g
IP Rating	IP60
Operation temperature	-10℃~+50℃(14°F~122°F)
Operation humidity	<85%RH (Non-condensation)

Dimensions

