

SAFETY DATA SHEET



Conforms to Regulation (EC) No. 1907/2006 (REACH), Annex II - United Kingdom (UK)

Sika® Drive Restorer

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name : Sika® Drive Restorer

1.2 Relevant identified uses of the substance or mixture and uses advised against

At present there is no complete information available on identified uses. When the data becomes available, it will be integrated into the safety data sheet.

Not available.

1.3 Details of the supplier of the safety data sheet

Manufacturer/Distributor : Sika Limited
Watchmead Welwyn Garden City
Hertfordshire. AL7 1BQ
United Kingdom

Telephone no.: : 01707 394444

Fax no. : 01707 329129

e-mail address of person responsible for this SDS : EHS@uk.sika.com

Emergency telephone number : +44 (0)1707 363899 (available during office hours).

1.4 Emergency telephone number

Supplier

Telephone number : +44 (0)1707 363899 (available during office hours).

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Product definition : Mixture

Classification according to Directive 1999/45/EC [DPD]

The product is not classified as dangerous according to Directive 1999/45/EC and its amendments.

Classification : Not classified.

See Section 16 for the full text of the R phrases or H statements declared above.

See Section 11 for more detailed information on health effects and symptoms.

2.2 Label elements

Hazard symbol or symbols :

Indication of danger :

Risk phrases : This product is not classified according to EU legislation.

Safety phrases : Not applicable.

Hazardous ingredients : Isotridecanol, ethoxylated

Supplemental label elements : Safety data sheet available for professional user on request.

SECTION 2: Hazards identification

Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles :

2.3 Other hazards

Other hazards which do not result in classification : Not available.

SECTION 3: Composition/information on ingredients

Substance/mixture : Mixture

Product/ingredient name Identifiers	%	Classification		Type
		67/548/EEC	Regulation (EC) No. 1272/2008 [CLP]	
Isotridecanol, ethoxylated EC: 500-027-2 CAS: 9043-30-5	>=1, <3	Xn; R22 Xi; R41 See Section 16 for the full text of the R-phrases declared above.	Acute Tox. 4, H302 Eye Dam. 1, H318 See Section 16 for the full text of the H statements declared above.	[1]

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs or vPvBs or have been assigned a workplace exposure limit and hence require reporting in this section.

Type

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

[3] Substance meets the criteria for PBT according to Regulation (EC) No. 1907/2006, Annex XIII

[4] Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII

[5] Substance of equivalent concern

Occupational exposure limits, if available, are listed in Section 8.

SECTION 4: First aid measures**4.1 Description of first aid measures**

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Get medical attention.
- Inhalation** : Get medical attention if symptoms occur.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.
- Ingestion** : Do not induce vomiting unless directed to do so by medical personnel. Maintain an open airway. Seek immediate medical attention.

4.2 Most important symptoms and effects, both acute and delayed**Potential acute health effects**

Eye contact : No known significant effects or critical hazards.

Inhalation : No known significant effects or critical hazards.

SECTION 4: First aid measures

Skin contact : No known significant effects or critical hazards.

Ingestion : No known significant effects or critical hazards.

Over-exposure signs/symptoms

Eye contact : No specific data.

Inhalation : No specific data.

Skin contact : No specific data.

Ingestion : No specific data.

4.3 Indication of any immediate medical attention and special treatment needed

Notes to physician : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

Specific treatments : No specific treatment.

SECTION 5: Firefighting measures**5.1 Extinguishing media**

Suitable extinguishing media : Use dry chemical, CO₂, water spray (fog) or foam.

Unsuitable extinguishing media : None known.

5.2 Special hazards arising from the substance or mixture

Hazards from the substance or mixture : In a fire or if heated, a pressure increase will occur and the container may burst.

Hazardous thermal decomposition products : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide

5.3 Advice for firefighters

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures**6.1 Personal precautions, protective equipment and emergency procedures**

For non-emergency personnel : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Put on appropriate personal protective equipment.

For emergency responders : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also Section 8 for additional information on hygiene measures.

6.2 Environmental precautions

: Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

SECTION 6: Accidental release measures

6.3 Methods and materials for containment and cleaning up

- Small spill** : Stop leak if without risk. Move containers from spill area. Absorb with an inert material and place in an appropriate waste disposal container.
- Large spill** : Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13).

6.4 Reference to other sections

- : See Section 1 for emergency contact information.
See Section 8 for information on appropriate personal protective equipment.
See Section 13 for additional waste treatment information.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Avoid contact with eyes, skin and clothing. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use.
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination.

7.3 Specific end use(s)

- Recommendations** : Not available.
- Industrial sector specific solutions** : Not available.

SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. Information is provided based on typical anticipated uses of the product. Additional measures might be required for bulk handling or other uses that could significantly increase worker or exposure or environmental releases.

8.1 Control parameters

Occupational exposure limits

No exposure limit value known.

- Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to European Standard EN 689 for methods for the assessment of exposure by inhalation to chemical agents and national guidance documents for methods for the determination of hazardous substances.

SECTION 8: Exposure controls/personal protection**DNELs/DMELs**

No DELs available.

PNECs

No PECs available.

8.2 Exposure controls

Appropriate engineering controls : Good general ventilation should be sufficient to control worker exposure to airborne contaminants. If this product contains ingredients with exposure limits, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure below any recommended or statutory limits.

Individual protection measures

Hygiene measures : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing.

Eye/face protection : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts.

Skin protection

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Reference number EN 374. Recommended: Butyl rubber/nitrile rubber gloves.

Body protection : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product. Recommended: Use barrier skin cream.

Other skin protection : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Respiratory protection : No special measures required.

Environmental exposure controls : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties**9.1 Information on basic physical and chemical properties****Appearance**

Physical state : Liquid.
Colour : Black.
Odour : Faint odour.
Odour threshold : Not available.
pH : ~8
Melting point/freezing point : Not available.
Initial boiling point and boiling range : Not available.
Flash point : Not available.
Evaporation rate : Not available.
Flammability (solid, gas) : Not available.
Burning time : Not applicable.
Burning rate : Not applicable.

SECTION 9: Physical and chemical properties

Upper/lower flammability or explosive limits	: Not available.
Vapour pressure	: Not available.
Vapour density	: Not available.
Density	: ~0.3 g/cm ³
Relative density	: Not available.
Solubility(ies)	: Soluble in the following materials: water
Partition coefficient: n-octanol/ water	: Not available.
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Viscosity	: Not available.
Explosive properties	: Not available.
Oxidising properties	: Not available.

9.2 Other information

No additional information.

SECTION 10: Stability and reactivity

10.1 Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
10.2 Chemical stability	: The product is stable.
10.3 Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
10.4 Conditions to avoid	: No specific data.
10.5 Incompatible materials	: No specific data.
10.6 Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information**11.1 Information on toxicological effects****Acute toxicity**

Product/ingredient name	Result	Species	Dose	Exposure
1,2-benzisothiazol-3(2H)-one	LD50 Oral	Rat	500 mg/kg	-

Conclusion/Summary : Not available.

Irritation/Corrosion

Conclusion/Summary : Not available.

Sensitisation

Conclusion/Summary : Not available.

Mutagenicity

Conclusion/Summary : Not available.

Carcinogenicity

SECTION 11: Toxicological information

Conclusion/Summary : Not available.

Reproductive toxicity

Conclusion/Summary : Not available.

Teratogenicity

Conclusion/Summary : Not available.

Information on the likely routes of exposure : Not available.

Potential acute health effects

Eye contact : May cause eye irritation.

Inhalation : May cause irritation.

Skin contact : May cause skin irritation.

Ingestion : Can cause gastrointestinal disturbances.

Delayed and immediate effects and also chronic effects from short and long term exposure**Short term exposure**

Potential immediate effects : Not available.

Potential delayed effects : Not available.

Long term exposure

Potential immediate effects : Not available.

Potential delayed effects : Not available.

Potential chronic health effects

Not available.

Conclusion/Summary : Not available.

General : No known significant effects or critical hazards.

Carcinogenicity : No known significant effects or critical hazards.

Mutagenicity : No known significant effects or critical hazards.

Teratogenicity : No known significant effects or critical hazards.

Developmental effects : No known significant effects or critical hazards.

Fertility effects : No known significant effects or critical hazards.

Other information : Not available.

SECTION 12: Ecological information**12.1 Toxicity**

Product/ingredient name	Result	Species	Exposure
1,2-benzisothiazol-3(2H)-one	Acute EC50 3 mg/l	Daphnia	48 hours

Conclusion/Summary : Not available.

12.2 Persistence and degradability

Conclusion/Summary : Not available.

12.3 Bioaccumulative potential

Not available.

12.4 Mobility in soil

SECTION 12: Ecological information

Soil/water partition coefficient (K_{oc}) : Not available.

Mobility : Not available.

12.5 Results of PBT and vPvB assessment

PBT : Not applicable.

vPvB : Not applicable.

12.6 Other adverse effects : No known significant effects or critical hazards.

SECTION 13: Disposal considerations**13.1 Waste treatment methods****Product**

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

Hazardous waste : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 91/689/EEC.

European waste catalogue (EWC)

Waste code	Waste designation
08 04 10	waste adhesives and sealants other than those mentioned in 08 04 09

Packaging : Completely emptied packaging or practically empty packaging containing dried/cured residues, once relieved of all pressure can be disposed of as non-hazardous waste.

Packaging may still contain hazardous residues and disposal should undertaken by a licensed waste contractor.

Any disposal practice must be in compliance with local and national laws and regulations.

SECTION 14: Transport information

	ADR/RID - ADN	IMDG	IATA
14.1 UN number	Not regulated.	Not regulated.	Not regulated.
14.2 UN proper shipping name	Diuron, Carbendazim	Diuron, Carbendazim	Diuron, Carbendazim
14.3 Transport hazard class(es)	-	-	-
14.4 Packing group	-	-	-
14.5 Environmental hazards	No	No	No
Additional information	-	-	-

SECTION 14: Transport information

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code : Not available.

SECTION 15: Regulatory information**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture****EU Regulation (EC) No. 1907/2006 (REACH)****Annex XIV - List of substances subject to authorisation****Annex XIV**

None of the components are listed (=> 0.1 %).

Substances of very high concern

None of the components are listed (=> 0.1 %).

Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles : Not applicable.

VOC content (EU) : VOC (w/w): 3.09%

Other EU regulations

REACH Information: : All substances contained in our Products are
 - preregistered or registered by our upstream suppliers, and/or
 - preregistered or registered by us, and/or
 - excluded from the regulation, and/or
 - exempted from the registration.

Europe inventory : Not available.

References : Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (CHIP 4)
 Control of Substances Hazardous to Health Regulations 2002 (COSHH) (as amended)
 Health & Safety at Work Act 1974
 The Environmental Protection (Duty of Care) Regulations 1991
 The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2007

Guidance Publications : Approved Code of Practice - Management of Health and Safety at Work, HSE
 General Approved Code of Practice to COSHH Regulations, HSE.

15.2 Chemical Safety Assessment : This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

Indicates information that has changed from previously issued version.

Abbreviations and acronyms : ATE = Acute Toxicity Estimate
 CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
 DNEL = Derived No Effect Level
 EUH statement = CLP-specific Hazard statement
 PNEC = Predicted No Effect Concentration
 RRN = REACH Registration Number

SECTION 16: Other information

Full text of abbreviated H statements	: H302 Harmful if swallowed. H318 Causes serious eye damage. H319 Causes serious eye irritation.
Full text of classifications [CLP/GHS]	: Acute Tox. 4, H302 ACUTE TOXICITY: ORAL - Category 4 Eye Dam. 1, H318 SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 1 Eye Irrit. 2, H319 SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 2
Full text of abbreviated R phrases	: R22- Harmful if swallowed. R41- Risk of serious damage to eyes.
Full text of classifications [DSD/DPD]	: Xn - Harmful Xi - Irritant

History

Date of printing	: 02.12.2013.
Date of issue	: 02.12.2013.
Date of previous issue	: 29.11.2013.

Notice to reader

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.