

**LED
20,000
LUMENS**




Hazardous Location SceneStar™ ELSS-XLAC-HDPL, ELSS-XLAC-HDPD

The SceneStar LED Scene Light is ideal for use in remote hazardous locations. With an output of 20,000 lumens, it provides operators with a flexible solution to use in areas where flammable vapors or gases may be present in sufficient quantities to be explosive or ignitable. It has been UL listed to UL 844 for Class I Division 2 Groups B, C and D.

Since LEDs are virtually indestructible, the SceneStar is ideal for use in a wide range of applications:

- Petroleum refineries and gasoline storage and dispensing areas
- Utility gas plants, and operations involving storage and handling of liquefied petroleum gas or natural gas
- Service applications associated with the transportation and / or storage of flammable gases
- Aircraft hangars and fuel servicing areas
- Spray finishing areas

- Available in 120VAC only
- Portable and Quad POD configurations only
- Cord lengths of 5, 25 or 50 ft (1.5, 7.6, 15.2 m) with a standard 3-prong 120VAC hazardous area plug
- Cord carrying strap included with Quad POD






ELSS-XLAC-HDPL

ELSS-XLAC-HDPD

330.264.5678 | 1.800.228.1161 | www.akronbrass.com | custserv@akronbrass.com

© Copyright 2014 Akron Brass Company. All rights reserved. No portion of this can be reproduced without the express written consent of the Akron Brass Company. (04/14)

SceneStar optics were designed to illuminate your entire scene, near and far.



SceneStar™ LED Scene Light ELSS-SLDC, ELSS-XLDC, and ELSS-XLAC

The SceneStar LED High Power Scene Light has been engineered to provide maximum visibility across your emergency scene with exceptional light output. The scene light features the latest in LED technology, vibrant white light, low operating temperatures, engineered optical control and the Akron Brass quality you have come to expect. Solid-state electronics ensure a lifetime of peak performance. The SceneStar is a brilliant combination of performance, durability, efficiency and style.

- Available in AC and DC versions
- Outstanding light output and overall illumination
- Optimized thermal management reduces LED temperatures for long life and reliability
- Streamlined aesthetics in a compact design
- Low ultraviolet light reduces insects during nighttime operation
- Standard powder coat paint in white (Black optional)*
- Heavy-duty 6 year warranty
- Serviceable construction

Mounting Options:

- Tripod
- Pole
- Portable
- Recessed
- Brow
- Fixed
- Under Aerial

*Handles and heat sink always black





SceneStar™ (220W)




Quartz Halogen (500W)



Brighter White Light Using Less Power
SceneStar LED Vs. Quartz Halogen



SceneStar LED Scene Light Base Types

Tripod	Quadpod	Portable Base (ELSS-XLAC-W-HDPL-50)	Portable Base (ELSS-XLAC-W-PL163B31-2P)
			

SceneStar LED Scene Light Specifications

Part Number	Base Type	Scene Light Type	Wattage	Voltage	Amps	Lumens
ELSS-XLAC-W-PL163B31-2P	Portable	Standard	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm
ELSS-XLAC-W-PDTBT1-NB-2P	130" Tripod	Standard	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm
ELSS-XLAC-W-PDTBT2-NB-2P	86" Tripod	Standard	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm
ELSS-XLAC-W-PDTBT3-NB-2P	71" Tripod	Standard	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm
ELSS-XLAC-W-PDTBT4-NB-2P	108" Tripod	Standard	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm
ELSS-XLAC-W-PDTBT5-NB-2P	55" Tripod	Standard	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm
ELSS-XLAC-W-HDPL-50	Portable	Hazardous Location	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm
ELSS-XLAC-W-HDPDTBQ3-50	82" Quadpod	Hazardous Location	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm
ELSS-XLAC-W-HDPDTBQ4-50	99" Quadpod	Hazardous Location	220 W	120 VAC / 240 VAC	1.8 A / 0.9 A	20,000 lm